

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190670104

Status:

Active

Overview:

Solderless Terminals

Description:

NylaKrimp Funnel Entry Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 5/16" (M8)

Documents:

3D Model

Product Specification PS-19902-013-001 (PDF)

3D Model (PDF)

Product Specification PS-19902-016-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-19902-011-001 (PDF)

Agency Certification

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19067

Crimp Quality Equipment

Yes

Overview

Solderless Terminals

Product Name

NylaKrimp

Taxonomy

Ring and Spade Terminals

Type

Ring

UPC

800753066908

Physical

Barrel Type

Closed - Brazed

Flammability

94V-2

Insulation

Nylon (PA)

Material - Plating Mating

Tin

Net Weight

23.932/g

Packaging Type

Bag

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Stud Size

5/16" (M8)

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

17.27mm max.

Wire Size AWG

1/0

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

H-981-56


Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001, PS-19902-016-001

Sales Drawing

SD-19067-007-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19067 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Manual Putt Pump Hydraulic System, Die set required

192860117

Die Set (large) for the HHLS Hydraulic Crimper

192890011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION