

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151330300

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

Pico-Clasp-to-Pico-Clasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 50.00mm Length, 3 Circuits, White



Documents:

[3D Model](#)

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	15133
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Pico-Clasp-to-Pico-Clasp
Overmolded	No
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	191128138857
Physical	
Cable Length	50.00mm
Circuits (Loaded)	3
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.355/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.60mm
Wire Size AWG	28
Wire/Cable Type	UL 1571
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	50V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2012341663-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

15133 Series

Mates With

Pico-Clasp Vertical Header [501940](#) , [203560](#) , [203561](#) . Pico-Clasp Right Angle Header [501953](#) , [203562](#) , [203563](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION