

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0334810601

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Mat-Sealed Male Connector Assembly, Single Row, 6 Circuits, Keying Option A, Black

Documents:	
Drawing (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model (PDF)	Application Specification AS-33472-100-FR-001 (PDF)
3D Model	Packaging Specification PK-31300-635-001 (PDF)
Product Specification PS-33471-000-001 (PDF)	Datasheet (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179

General	
Product Family	Crimp Housings
Series	33481
Application	Power, Wire-to-Wire
Overview	MX150 Connector System
Product Name	MX150
Taxonomy	Connector Housings
UPC	756054494370

Physical	
Circuits (maximum)	6
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	11.838/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33472-100-FR-001
Packaging Specification	PK-31300-635-001
Product Specification	PS-33471-000-001
Sales Drawing	PK-31300-903-001, SD-33481-061-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

33481 Series

Mates With

MX150 Sealed Single Row Female Connector [33471](#)

Use With

MX150 Male Terminal [33000](#) , [33011](#)

MX150 Sealed Blade Cavity Plug [343450001](#)

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION