

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0428786506

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Vertical, Low Profile, 6/2

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-42878-001 (PDF)


Packaging Specification PK-42878-492-001 (PDF)

Test Summary TS-42878-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		42878
Comments		Flush Mount, Flangeless, 2 PCB Thick
Component Type		PCB Jack
Magnetic		No
Overview		Magnetic and Modular Jacks/Plugs
Performance Category		3
Power over Ethernet (PoE)		N/A
Product Name		Modular Jack 6/2
Taxonomy		Modular Jacks and Plugs
UPC		800753826786

Physical		
Boot Color		N/A
Color - Resin		Black
Durability (mating cycles max)		500
Flammability		94V-0
Inverted / Top Latch		N/A
Jack Height		12.70mm
Lightpipes/LEDs		None
Material - Metal		Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Polyester
Net Weight		1.766/g
Orientation		Vertical (Top Entry)
PCB Locator		Yes
PCB Retention		Yes
PCB Thickness - Recommended		1.57mm
Packaging Type		Tray
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.27mm
Plating min - Mating		1.270µm
Plating min - Termination		2.540µm
Port Configuration		1x1
Positions / Loaded Contacts		6/2
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		-40° to +85°C
Termination Interface: Style		Through Hole
Waterproof / Dustproof		No
Wire/Cable Type		N/A



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

42878 Series

Mates With

FCC 68 Plugs

Electrical

Current - Maximum per Contact	1.5A
Shielded	No
Voltage - Maximum	150V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-42878-492-001
Product Specification	PS-42878-001
Sales Drawing	SDA-42878-XXXX-001
Test Summary	TS-42878-001-001

This document was generated on 10/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION