

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0310671071

Status:


Active

Overview:

H-DAC 64 Unsealed Connector System

Description:

2.54mm H-DAC 64, 3 Way Male Housing Assembly, Single Row, Polarization B, with Xmas Tree Attachment, Gray



Series image - Reference only

Documents:	
3D Model	Application Specification AS-31067-100-001 (PDF)
3D Model (PDF)	Packaging Specification PK-30907-737-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-076-001 (PDF)
Product Specification PS-31067-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General		EU ELV	
Product Family	Crimp Housings	Compliant	
Series	31067		
Application	Automotive, Power, Wire-to-Wire	EU RoHS	
Comments	Polarization Option B, Gray	Compliant	
Overview	H-DAC 64 Unsealed Connector System	China RoHS	
Product Name	H-DAC 64	REACH SVHC	
Taxonomy	Connector Housings	Not Contained Per -	
UPC	800756477152	D(2022)4187-DC (10	
Physical		June 2022)	
Circuits (maximum)	3	Halogen-Free	
Color - Resin	Gray	Status	
Gender	Plug	Low-Halogen	
Glow-Wire Capable	No	For more information, please visit Contact US	
Keying to Mating Part	None	China ROHS	
Lock to Mating Part	Yes	ELV	
Material - Resin	Modified Polystyrene, Polyester	RoHS Phthalates	
Net Weight	2.044/g	Green Image	
Number of Rows	1	Compliant	
Packaging Type	Bag	Not Contained	
Panel Mount	No		
Pitch - Mating Interface	2.54mm		
Pitch - Termination Interface	2.54mm		
Polarized to Mating Part	Yes		
Ports	1		
Stackable	No		
Temperature Range - Operating	-40° to +100°C		
Electrical			
Current - Maximum per Contact	11.0A, 9.0A		
Solder Process Data			
Lead-freeProcess Capability	N/A		
Material Info			
Reference - Drawing Numbers			
Application Specification	AS-31067-100-001		
Packaging Specification	PK-30907-737-001, PK-31301-076-001		
Product Specification	PS-31067-0001-001		
Sales Drawing	SD-31110-003-001		

Search Parts in this Series
31067 Series

Mates With
H-DAC 64 3 Way Receptacle Assembly
310671011

Use With
See Product Specification

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION