

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015246041

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit BMI Header, 4.20mm Pitch, Dual Row, Vertical, with Snap-in Plastic Peg PCB Lock, 4 Circuits, PA Polyamide Nylon 6/6, UL 94V-2, Tin (Sn) Plating, without Drain Holes

Documents:	
3D Model	Product Specification PS-5556-002-001 (PDF)
Drawing (PDF)	Packaging Specification PK-42440-001-001 (PDF)
3D Model (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification 55560002-PS-CH-000 (PDF)	Symbol Footprint Data SYM-A42440-04XX-001 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 55560002-PS-SK-000 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	42440
Application	Board-to-Board, Power, Wire-to-Board
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus HCS Crimp Terminal Crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current de-rating information.
Component Type	PCB Header
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit BMI
Taxonomy	PCB Headers and Receptacles
UPC	800753534995
Physical	
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.284/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.56mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
Packaging Type	Tray
Pitch - Mating Interface	4.20mm



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

42440 Series

Mates With

[15060040](#) Mini-Fit BMI Panel Mount Receptacle, [15247040](#) Mini-Fit BMI Vertical Receptacle Header, [39013042](#) Mini-Fit Jr. Receptacle, [245135](#) Mini-Fit Jr. Cable Assembly

Plating min - Mating	2.540μm
Plating min - Termination	2.540μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	240
Material Info	
Engineering Number	A-42440-0411
Reference - Drawing Numbers	
Packaging Specification	PK-42440-001-001
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-5556-002-001
Sales Drawing	SDA-42440-XXXX-001
Symbol/Footprint Data	SYM-A42440-04XX-001
Test Summary	TS-5556-002-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION