

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2177901123

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Squba 1.8 Female-to-Squba 1.8 Female, Tin (Sn) Plating, 225.00mm Length, 22 AWG, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

|                                |                                 |
|--------------------------------|---------------------------------|
| General                        |                                 |
| Product Family                 | Cable Assemblies                |
| Series                         | 217790                          |
| Assembly Configuration         | Pre-crimped Lead Only           |
| Connector to Connector         | Squba Crimp Terminals           |
| Overview                       | Off-the-Shelf Pre-Crimped Leads |
| Product Name                   | Squba                           |
| Taxonomy                       | Power and Signal Cable Assembl  |
| UPC                            | 195842123793                    |
| Physical                       |                                 |
| Cable Length                   | 225.00mm                        |
| Circuits (Loaded)              | 1                               |
| Color - Resin                  | Black                           |
| Gender                         | Female-Female                   |
| Lock to Mating Part            | Yes                             |
| Material - Metal               | Copper Alloy                    |
| Material - Plating Mating      | Tin                             |
| Material - Plating Termination | Tin                             |
| Material - Resin               | PVC                             |
| Net Weight                     | 1.146/g                         |
| Number of Rows                 | 1                               |
| Packaging Type                 | Bag                             |
| Single Ended                   | No                              |
| Termination Interface: Style   | Crimp or Compression            |
| Wire Insulation Diameter       | 0.95mm-1.40mm                   |
| Wire Size AWG                  | 22                              |
| Wire/Cable Type                | UL 10002                        |
| Electrical                     |                                 |
| Current - Maximum per Contact  | 6.0A                            |
| Voltage - Maximum              | 125V                            |
| Material Info                  |                                 |
| Reference - Drawing Numbers    |                                 |
| Sales Drawing                  | 2177901121-000                  |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

217790 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION