

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2002411215

Status:

Active

Overview:

Mega-Fit Power Connectors

Description:

Mega-Fit Right-Angle Header, Single Row, 5.70mm Pitch, 5 Circuits, 1.52µm Matte Tin Plating, UL 94V-0, Glow-Wire Capable, Black

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification 1720631000-PS-000 (PDF)

Application Specification 768232000-AS-000 (PDF)

Packaging Specification 2002412000-001 (PDF)

Test Summary 1720631000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		152514
UL		E29179
General		
Product Family		PCB Headers
Series		200241
Application		Power, Wire-to-Board
Component Type		PCB Header
Overview		Mega-Fit Power Connectors
Product Name		Mega-Fit
Taxonomy		PCB Headers and Receptacles
UPC		191130086689

Physical	
Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	3.550/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.60mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm, 2.36mm
Packaging Type	Tray
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	1.524µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

200241 Series

Mates With

Mega-Fit Receptacle Housing 200456

Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	26.0A
Voltage - Maximum	600V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	768232000-AS-000
Packaging Specification	2002412000-001
Product Specification	1720631000-PS-000
Sales Drawing	2002412000-000
Test Summary	1720631000-TS-000

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION