

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192110001](#)
Status: **Active**
Overview: [Wire Pins](#)
Description: Krimptite Wire Pin Terminal for 12-10 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Crimp Terminals
 Series [19211](#)
 Application Power, Wire-to-Component
 Comments Pin Length 11.43mm
 Crimp Quality Equipment Yes
 Overview [Wire Pins](#)
 Packaging Alternative [192110002](#) (Adhesive Tape on Reel)
 Product Name Wire Pin
 Taxonomy Crimp Terminals
 UPC 800755061994

Physical

Gender Male
 Material - Metal Copper
 Material - Plating Mating Tin
 Net Weight 1.465/g
 Packaging Type Bag
 Plating min - Mating 1.016µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 3.45mm max.
 Wire Size AWG 10, 12
 Wire Size mm² N/A

Material Info

Engineering Number WP-1210

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19211-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19211 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade [640030100](#)

Hand Crimp Tool for
 Krimptite/Versakrimp
 Terminals and
 Splices, 10-22
 AWG and 6.0mm² -
 0.5mm²

Crimp Head for the [640070100](#)

AT-200 Pneumatic
 Hand Tool

ServiceGrade Hand [640160038](#)

Crimp Tool - Ratchet

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION