

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0875683463

Status:

Active

Overview:

Milli-Grid Connector System

Description:

Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 34 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp

Documents:

- 3D Model

Application Specification 503940002-AS-000 (PDF)
- Drawing (PDF)

Packaging Specification PK-87568-0001-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-87568-004-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

IDT and Solder Connectors

Series

87568

Crimp Quality Equipment

Yes

Overview

Milli-Grid Connector System

Product Name

Milli-Grid

Taxonomy

Connector Housings

UPC

822348458110

Use With

875691034 Strain Relief (Optional)

Physical

Circuits (Loaded)

34

Circuits (maximum)

34

Color - Resin

Black

Durability (mating cycles max)

100

Flammability

94V-0

Gender

Female

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Copper Alloy

Material - Plating Mating

Gold

Material - Resin

Polyester

Net Weight

1.896/g

Number of Rows

2

Packaging Type

Tray

Panel Mount

No

Pitch - Mating Interface

2.00mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-20° to +85°C

Termination Interface: Style

IDT or Pierce

Wire Size AWG

28

Electrical

Current - Maximum per Contact

1.0A

Voltage - Maximum

125V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

87568 Series

Mates With

87831 Vertical PCB Header, 87832 Surface Mount PCB Header, 87833 Right Angle PCB Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
IDT - Manual - Handtool	621002000
Manual Press with IDT Ribbon Cable Tool Kit	621002200
IDT Ribbon Cable Adapter Kit for 2.00mm	621002400

Reference - Drawing Numbers

Application Specification	503940002-AS-000
Packaging Specification	PK-87568-0001-001
Product Specification	PS-87568-004-001
Sales Drawing	SD-87568-003-001

IDT - Manual - Tool 621003200
Kit

This document was generated on 12/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION