

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528072410

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 24 Circuits

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification PS-52807-003-001 (PDF)

Packaging Specification SPK-52807-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

Taxonomy

UPC

FFC/FPC Connectors

52807

Easy-On FFC FPC Connectors

Easy-On

FFC / FPC Connectors

800754361330

Physical

Actuator Type

Circuits (Loaded)

Color - Resin

Contact Position

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire/Cable Type

Non-ZIF

24

Natural

Top

94V-0

3.60mm

Phosphor Bronze

Tin

Tin

High Temperature Thermoplastic

728.001/mg

1

Right Angle

3.20mm

Through Hole - Kinked Pin

None

Tray

1.00mm

1.00mm

0.914µm

0.914µm

Yes

No

No

-20° to +80°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.2A, 0.4A, 0.5A

50V

Material Info

Reference - Drawing Numbers

Packaging Specification

SPK-52807-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52807 Series

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION