

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0905841320

Status:


Active

Overview:

Picoflex Ribbon-Cable Connectors

Description:

1.27mm Pitch Picoflex PF-50 IDT Receptacle, Low Profile, Board-in, 20 Circuits



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification 908140000-AS-000 (PDF)
3D Model	Packaging Specification PK-90584-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-99020-0011-001 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	Ribbon Cable / Wire Trap Connectors
Series	90584
Comments	Low Profile
Component Type	One Piece
Gender	Receptacle
Glow-Wire Capable	No
Overview	Picoflex Ribbon-Cable Connectors
Product Name	Picoflex
Taxonomy	Connector Housings
UPC	800753662063
Physical	
Circuits (Loaded)	20
Color - Resin	Natural
Durability (mating cycles max)	30
Entry Angle	90° Angle
Flammability	94V-0
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.300/g
Number of Rows	2
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	1.27mm
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Polarized to Mating Part	N/A
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Kinked Pin
Wire Insulation Diameter	1.00mm max.
Wire Size AWG	26, 28
Wire/Cable Type	Ribbon Cable
Electrical	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90584 Series

Mates With

N/A

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Picoflex PF-50 IDT Receptacle, 4-26 Circuits, 26 or 28 AWG Flat Cable, 1.00mm max. thickness	690081090
Arbor Press Fixture	690201902
Arbor Press Fixture	690201908

Current - Maximum per Contact	1.2A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Reference - Drawing Numbers	
Application Specification	908140000-AS-000
Packaging Specification	PK-90584-001-001
Product Specification	PS-99020-0011-001
Sales Drawing	SDA-90584-001, SDA-90584-002

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION