

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0022112122
Status:	Active
Overview:	KK Interconnect Systems
Description:	KK 254 Solid Header, Vertical, with Friction Lock, 12 Circuits, Gold (Au) Plating

Documents:

3D Model	Packaging Specification PK-6373-001-000 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-22-23-2121-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-10-07-001 (PDF)	



Series image - Reference only

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	<u>6373</u>
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	<u>KK Interconnect Systems</u>
Product Name	KK 254
Taxonomy	PCB Headers and Receptacles
UPC	800753592636

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Natural (White)
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	Nylon
Net Weight	1.372/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.56mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

6373 Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-6373-12A241
Reference - Drawing Numbers	
Packaging Specification	PK-6373-001-000
Product Specification	PS-10-07-001
Sales Drawing	SD-6373-001-000, SD-6373-001-002
Symbol/Footprint Data	SYM-22-23-2121-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION