

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5016471100

Status:

Active

Overview:

iGrid Wire-to-Board Dual-Row System

Description:

2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag

- Documents:
- 3D Model (PDF)

Application Specification 5016460000-A00 (PDF)
- 3D Model

Application Specification 5016460000-A01 (PDF)
- Drawing (PDF)

Packaging Specification 5016479200-200 (PDF)
- Product Specification 5016461001-PS-001 (PDF)

Datasheet (PDF)
- Product Specification PS-501646-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	501647
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	iGrid Wire-to-Board Dual-Row System
Packaging Alternative	5016471000 (Reel)
Product Name	iGrid
Taxonomy	Crimp Terminals
UPC	822350087292

Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	76.000/mg
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95-1.50mm
Wire Size AWG	22, 24, 26
Wire Size mm²	0.126-0.34

Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	5016460000-A00, 5016460000-A01
Crimp Specification	5016470000-CS-000
Packaging Specification	5016479200-200
Product Specification	5016461001-PS-001, PS-501646-001-001
Sales Drawing	5016470000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

501647 Series

Use With

iGrid Receptacle Housing 501646

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	638131500
PremiumGrade Hand Crimp Tool for iGrid Female Terminals, 22-26 AWG and 0.30-0.20mm² Wire	638192300

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION