

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0038000887](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: KK Header, Vertical, with Polarizing Backwall, 7 Circuits, Tin (Sn) Plating, Circuit 4 Voided

Documents:

[Drawing \(PDF\)](#) [Symbol Footprint Data SYM-1008-5071-001 \(PDF\)](#)
[Product Specification PS-99020-0087-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-2599-0001-000 \(PDF\)](#)

Agency Certification


UL E29179

General

Product Family PCB Headers
Series [2599](#)
Application Signal, Wire-to-Board
Component Type PCB Header
Overview [KK Interconnect Systems](#)
Product Name KK 508
Taxonomy PCB Headers and Receptacles
UPC 800753732315

Physical

Breakaway No
Circuits (Loaded) 6
Circuits (maximum) 7
Color - Resin Natural
Durability (mating cycles max) 25
First Mate / Last Break No
Flammability 94V-2
Glow-Wire Capable No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.713/g
Number of Rows 1
Orientation Vertical
PC Tail Length 4.45mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Plating min - Mating 5.080µm
Plating min - Termination 5.080µm
Polarized to Mating Part Yes
Polarized to PCB No
Shrouded Partial
Stackable No
Surface Mount Compatible (SMC) No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[2599](#) Series

Mates With

Crimp Housing [3001](#)
 PCB Receptacle [3002](#)

Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	4.5A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	2599M07A04
Reference - Drawing Numbers	
Packaging Specification	PK-2599-0001-000
Product Specification	PS-99020-0087-001
Symbol/Footprint Data	SYM-1008-5071-001

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION