

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039532065

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

1.25mm Pitch Easy-On FFC/FPC Connector, Through-Hole, Vertical, ZIF, 6 Circuits

Documents:	
3D Model (PDF)	Product Specification PS-5597-004-001 (PDF)
3D Model	Packaging Specification SPK-5597-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179

General	
Product Family	FFC/FPC Connectors
Series	5597
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Taxonomy	FFC / FPC Connectors
UPC	822348190010

Physical	
Actuator Type	Slider
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	30
Flammability	94V-0
Mated Height	7.50mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyester
Net Weight	677.750/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	No
PCB Mounting	Through Hole
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	FFC/FPC

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	200V

Material Info	
Engineering Number	5597-06CPB7F



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[5597](#) Series

Reference - Drawing Numbers

Packaging Specification	SPK-5597-001-001
Product Specification	PS-5597-004-001
Sales Drawing	SD-5597-007-001, SD-5597-007-002

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION