

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0530471310

Status:


Active

Overview:

PicoBlade Connector System

Description:

1.25mm Pitch, PicoBlade PCB Header, Single Row, Vertical, Through Hole, Tin Plating, Friction Lock, 13 Circuits, Tray, 2.30mm PC Tail Length



Documents:	
2D Drawing DXF (PDF)	Product Specification 510211110-PS-000 (PDF)
2D Drawing (DXF)	Application Specification 510210000-AS-000 (PDF)
3D Model (PDF)	Packaging Specification SPK-53047-001-001 (PDF)
3D Model	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 510211010-PS-000 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	53047
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	PicoBlade Connector System
Product Name	PicoBlade
Taxonomy	PCB Headers and Receptacles
UPC	800753565876
Physical	
Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	5.20mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	253.600/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

53047 Series

Mates With

PicoBlade Housing 51021

Temperature Range - Operating

Termination Interface: Style

-40° to +85°C

Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.0A

125V

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

510210000-AS-000

SPK-53047-001-001

510211010-PS-000, 510211110-PS-000

530470000-SD-000

This document was generated on 01/04/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION