

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015911043

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Breakaway Header, Surface Mount, Dual Row, Vertical, 4 Circuits, 0.76µm Gold (Au) Selective Plating, with 3.30mm PCB Locator Pegs

Documents:

- 3D Model

Application Specification 713080001-AS-000 (PDF)
- 3D Model (PDF)

Packaging Specification 713080001-PK-000 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-71308-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

71308

Application

Board-to-Board, Signal, Wire-to-Board

Component Type

PCB Header

Overview

C-Grid Connector Products

Product Name

C-Grid

Taxonomy

PCB Headers and Receptacles

UPC

800754395854

Physical

Breakaway

Yes

Circuits (Loaded)

4

Circuits (maximum)

4

Color - Resin

Black

Durability (mating cycles max)

50

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

0.263/g

Number of Rows

2

Orientation

Vertical

PCB Locator

Yes

PCB Retention

Yes

Packaging Type

Tube

Pitch - Mating Interface

2.54mm

Plating min - Mating

0.813µm

Plating min - Termination

2.032µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

Yes

Temperature Range - Operating

-40° to +120°C


Termination Interface: Style

Surface Mount

Electrical

Current - Maximum per Contact

3.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

71308 Series

Mates With

C-Grid Surface Mount Right-Angle PCB Receptacle [71979](#) . C-Grid Surface Mount Vertical PCB Receptacle [71395](#) . C-Grid Through-hole Vertical PCB Receptacle [71850](#) . C-Grid Shunt Terminal Housing [7859](#)

Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Engineering Number	71308-4204N
Reference - Drawing Numbers	
Application Specification	713080001-AS-000
Packaging Specification	713080001-PK-000
Product Specification	PS-71308-001
Sales Drawing	713080000-SD-000

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION