

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1718130003

Status:

Active

Overview:

KK Interconnect Systems

Description:

3.96mm Pitch, KK 396 RPC Vertical Header with Friction Lock, Tin (Sn) Plating, Pin Length 17.02mm, Bag, 3 Circuits, without Pegs



Series image - Reference only

Documents:

- 3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification PS-171813-0001-001 (PDF)

Product Specification PS-171813-0002-001 (PDF)
- Packaging Specification PK-41791-001-001 (PDF)

Test Summary TS-171813-0001-001 (PDF)

Symbol Footprint Data SYM-171813-0003-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Series

Application

Comments

PCB Headers

171813

Board-to-Board, Power, Signal, Wire-to-Board

See Product Specification for maximum current rating by material, AWG, and orientation; See Product Specification for operating temperature range by material.

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Header

KK Interconnect Systems

KK 396

PCB Headers and Receptacles

887191374703

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

No

3

3

Black

25

No

94V-1, 94V-2

No

No

None

Yes

Brass

Matte Tin

Matte Tin

High Temperature Thermoplastic

0.917/g

1

Vertical

No

None

1.60mm

Bag

3.96mm

1.524µm

1.524µm

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

171813 Series

Mates With

2145 , 41815 , 6442 , 2139 , 41695 , 3069

Polarized to Mating Part	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +80°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	5.0A, 7.0A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Cross-Plant Material Status	LT
Reference - Drawing Numbers	
Packaging Specification	PK-41791-001-001
Product Specification	PS-171813-0001-001, PS-171813-0002-001
Sales Drawing	SD-171813-0001-000, SD-171813-0001-002
Symbol/Footprint Data	SYM-171813-0003-001
Test Summary	TS-171813-0001-001

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION