

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022288063

Status:

Active

Overview:

Description:

KK 254 Breakaway Header, Right-Angle Surface Mount Compatible, 6 Circuits, 0.38µm Gold (Au) Selective Plating, Mating Pin Length 8.23mm

Agency Certification		
CSA		LR19980
UL		E29179
Application tooling part link		
Application Tooling Part Link		11-20-1230
General		
Product Family		PCB Headers
Series		42377
Application		Board-to-Board, Signal, Wire-to-Board
Component Type		PCB Header
Overview		kk
Product Name		KK 254
Taxonomy		PCB Headers and Receptacles
UPC		800754240093
Physical		
Breakaway		Yes
Circuits (Loaded)		6
Circuits (maximum)		6
Color - Resin		Black
Durability (mating cycles max)		100
Flammability		94V-0
Glow-Wire Capable		No
Lock to Mating Part		None
Material - Metal		Brass
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Net Weight		0.463/g
Number of Rows		1
Orientation		Right Angle
PC Tail Length		3.05mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Bag
Pitch - Mating Interface		2.54mm
Plating min - Mating		0.381µm
Plating min - Termination		2.540µm
Polarized to Mating Part		Yes
Polarized to PCB		No
Shrouded		Partial
Stackable		No
Surface Mount Compatible (SMC)		Yes
Temperature Range - Operating		See Product Specification
Termination Interface: Style		Through Hole
Electrical		
Current - Maximum per Contact		4.0A
Voltage - Maximum		500V

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42377 Series

Mates With

KK 254 Crimp Housing [2695](#) , [7880](#) . KK 254 Top-Entry PCB Receptacle [4455](#) . C-Grid Shunt Terminal Housing [7859](#)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	42377-0111
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-40873-0041-001
Product Specification	PS-10-07-001
Sales Drawing	SD-42377-001-000, SD-42377-001-002
Symbol/Footprint Data	SYM-22-28-8061-001

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION