

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022173032

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 254 PC Board Connector, Bottom Entry, 0.38µm Gold (Au) Selective, 3 Circuits

Documents:	
3D Model	Product Specification PS-10-07-001 (PDF)
3D Model (PDF)	Packaging Specification PK-44646-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General


Product Family	PCB Receptacles
Series	4455
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Overview	KK Interconnect Systems
Product Name	KK 254
Taxonomy	PCB Headers and Receptacles
UPC	800754932523

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural (White)
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.369/g
Number of Rows	1
Orientation	Bottom Entry
PC Tail Length	3.35mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	2.5A
Grounding to PCB	No
Voltage - Maximum	500V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[4455 Series](#)

Mates With

KK Header [4094](#) , [42376](#) , [42375](#) , [42377](#) ,
[4030](#) , [171856](#) , [171857](#)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-4455-BH03D(208)
--------------------	-------------------

Reference - Drawing Numbers

Packaging Specification	PK-44646-001-001
Product Specification	PS-10-07-001
Sales Drawing	SDA-4455-001

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION