

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022288031

Status:

Active

Overview:

[KK Interconnect Systems](#)

Description:

KK 254 Breakaway Header, Right-Angle Surface Mount Compatible, 3 Circuits, Tin (Sn) Plating, Mating Pin Length 8.23mm



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-40873-0041-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-22-28-8031-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-10-07-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
Application tooling part link	
Application Tooling Part Link	11-20-1230
General	
Product Family	PCB Headers
Series	42377
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Overview	KK Interconnect Systems
Product Name	KK 254
Taxonomy	PCB Headers and Receptacles
UPC	800754240048
Physical	
Breakaway	Yes
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.231/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[42377](#) Series

Mates With

KK 254 Crimp Housing [2695](#) , [7880](#) . KK 254 Top-Entry PCB Receptacle [4455](#) . C-Grid Shunt Terminal Housing [7859](#)

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	42377-0038
Reference - Drawing Numbers	
Packaging Specification	PK-40873-0041-001
Product Specification	PS-10-07-001
Sales Drawing	SD-42377-001-000, SD-42377-001-002
Symbol/Footprint Data	SYM-22-28-8031-001

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION