

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050842120

Status:

Active

Overview:

MLX Power Connectors

Description:

2.13mm Diameter MLX Pin and Socket Receptacle, 12 Circuits, Natural

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification PS-42022-0001-001 (PDF)

Packaging Specification PK-42022-XX-001 (PDF)

Test Summary TS-42022-0001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	42022
Application	Power, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 366440007; Maximum current per contact 20A if used with 36663 and 36664 terminal
Overview	MLX Power Connectors
Product Name	MLX
Taxonomy	Connector Housings
UPC	800754386876
Physical	
Circuits (maximum)	12
Circuits Detail	12
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	8.670/g
Number of Rows	3
Packaging Type	Carton
Panel Mount	Yes
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C
Electrical	
Current - Maximum per Contact	20.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	42022-12A
Reference - Drawing Numbers	
Packaging Specification	PK-42022-XX-001
Product Specification	PS-42022-0001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42022 Series

Mates With

MLX Power Crimp Housing Plug 42021

Use With

MLX Crimp Terminal 42023 , 42024 . MLX Male Pre-Crimped Lead 797582029 , 797582030 . MLX Female Pre-Crimped Lead 797582031 , 797582032

This document was generated on 10/07/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION