

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2074580006

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK Plus 396 Receptacle Housing, 3.96mm Pitch, Single Row, 6 Circuits, UL 94V-0, Black

Documents:	
3D Model	Product Specification 2074580000-PS-JP-000 (PDF)
3D Model (PDF)	Product Specification 2074580000-PS-SK-000 (PDF)
Drawing (PDF)	Product Specification 2074580000-TS-000 (PDF)
Product Specification 2074580000-PS-000 (PDF)	Packaging Specification 2074580000-PK-000 (PDF)
Product Specification 2074580000-PS-CH-000 (PDF)	Datasheet (PDF)
Product Specification 2074580000-PS-ES-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	207458
Application	Power, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK Plus
Taxonomy	Connector Housings
UPC	191130115600
Physical	
Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.090/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2074580000-PK-000
Product Specification	2074580000-PS-000, 2074580000-PS-CH-000, 2074580000-PS-ES-000, 2074580000-PS-JP-000, 2074580000-PS-SK-000, 2074580000-TS-000
Sales Drawing	2074580000-SD-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
207458 Series

Mates With
KK Plus 396 Headers 207478 , 207479

Use With
Female Crimp Terminal 455703000 , 455703002 , 455703050 , 455703052 . KK Plus 396 TPA Retainer 207459

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION