

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0353280260

Status:

Active

Description:

7.92mm Pitch Header, Vertical, Positive Lock, Shrouded, 2 Circuits, White, PA Polyamide (Nylon) 6/6, Glass-filled

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-35156-005-001 (PDF)

Packaging Specification PK-35328-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Product Name

Taxonomy

UPC

PCB Headers

35328

Power, Wire-to-Board

N/A

PCB Headers and Receptacles

822348697625

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

2

2

Natural

30

No

94V-0

No

No

None

Yes

Tin

Tin

Nylon

0.826/g

1

Vertical

3.40mm

No

None

1.60mm

Bag

7.92mm

5.080µm

5.080µm

Yes

No

Partial


No

Yes

-40° to +105°C

Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

35328 Series

Mates With

351560300 Wire-to-Board Housing

Current - Maximum per Contact

7.0A

Voltage - Maximum

250V

Material Info

Reference - Drawing Numbers

Packaging Specification

PK-35328-001-001

Product Specification

PS-35156-005-001

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION