

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0714393364

Status:


Active

Overview:

1.00mm Mezzanine (IEEE 1386)

Description:

1.00mm Mezz (IEEE 1386) Receptacle, Surface Mount, Dual Row, Vertical Stacking, Tube, 0.76µm Gold (Au), 64 Circuits Pick and Place Cap



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-70873-063-001 (PDF)
3D Model (PDF)	Packaging Specification PK-70873-0693-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-71436-9999-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	71439
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Overview	1.00mm Mezzanine (IEEE 1386)
Product Name	1.00mm Mezzanine (IEEE 1386)
Taxonomy	Board-to-Board Connectors
UPC	800754687805
Physical	
Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Natural
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	14.00mm, 15.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.534/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	100V

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

71439 Series

Mates With

71436 1.00mm Mezz (IEEE 1386) Plug. Be sure to match like stack heights

Solder Process Data

Lead-freeProcess Capability
Process Temperature max. C

REFLOW
260

Material Info

Reference - Drawing Numbers

Packaging Specification
Product Specification
Sales Drawing

PK-70873-063-001, PK-70873-0693-001
PS-71436-9999-001
714393000-000, SDA-71439-3XXX-002

This document was generated on 01/04/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION