
## Building Management





## ARANET OFFERS WIDE RANGE OF SENSORS:

ARANET PRO BASE STATION is an industrial grade wireless environmental monitoring solution. It has an internal memory and a built in webserver with free software for easy viewing, analysing and comparing data in real time as well as for setting thresholds for alarms and exporting reports. Base station gathers readings from wireless sensors within the range of up to 3 km/1.9 mi.

TEMPERATURE CENCORS		Measurement range	Battery*	IP class
air, liquid and solid surface temperature. The probe can be placed in liquids or places that require close contact temperature measurements, like heating pipes or soil. Use cases include air conditioning and ventilation systems (HVAC), food industry, pharmaceutical industry, R&D laboratories.	T-probe sensor	-55 °C to 105 °C -67 °F to +221 °F	10 years	IP68
	T Compact sensor	-40 °C to 60 °C -40 °F to 140 °F	7 years	IP68
	PT100 / PT1000 transmitter	-200 °C to 800 °C -328 °F to 1472 °F	10 years	IP68
	PT100 sensor*	-50 °C to 180 °C -58 °F to 356 °F	10 years	IP68
		Measurement range	Battery*	IP class
T/RH SENSORS measure temperature and relative humidity. Aranet sensors are extremely durable and can be placed in both inside and outside environments as well humid locations.	T/RH sensor	temperature: -40 °C to 60 °C	10 years	IP42
	T/RH IP67 sensor	0% to 100%	10 years	IP67
T/RH PROBES provide very accurate temperature and relative humidity measurements. Perfectly suitable also for harsh environments.	1	Measurement range	Battery*	IP class
	T/RH probe	temperature: -40°C to 85°C -40°F to 185°F, relative humidity: 0-100%	10 years	IP67
AMBIENT LIGHT SENSORS are wireless and battery-powered, made to easily monitor whether your building is sufficiently lit, as well as to see if you're not wasting energy on excess lighting.		Measurement range	Battery*	IP class
	LUX sensor	0 – 200 000 lux	7 years	IP68
		Measures	Battery*	IP class
for measuring the difference in air pressure between two points for applications in HVAC, building automation, clean rooms and more.	Differential Pressure sensor	Pressure range ± 500 Pa Accuracy 0.10 Pa + 3 % of reading	10 years	IP65
	_	Measurement range	Battery*	IP class
DISTANCE SENSOR works with all kinds of liquid or solid surfaces, for a broad range of practical applications, such as measuring the grain level in a silo, or the level of a liquid in a container.	Ultrasonic Distance sensor	0.3 to 5 m or 0.5 to 10 m	7 years	IP67
		Measurement range	Battery*	IP class
attery-powered and energy-efficient solutions designed to integrate with any 3rd party sensor that uses V/mA as an output. This solution allows the Aranet system to be opened up to virtually any parameter monitoring so that you can have all of your required sensors in a single system.	Voltage sensor	voltage (-32 to +32 VDC)	7 years	IP68
	4-20 mA sensor	current (0-30 mA)	7 years	IP68
		Measurement range	Battery**	IP class
	Dry Contact Pulse counter	Detects dry contact pulses. Perfect for electricity meters and water flow monitoring.	10 years	IP67

Dry Contact Hour

Aranet4 HOME

Aranet4 PRO

& iOS app

CO<sub>2</sub> and Temperature sensor

Meter

**GAS SENSORS** are designed for leak detection, workplace safety and personal safety. Aranet sensors are wireless, battery-powered and suitable for the most challenging environments.

**DRY CONTACT METERS** 

value from other gases.

**CO, SENSORS** have a built-in infrared CO<sub>2</sub> sensor that actually measures the real CO<sub>2</sub> gas content, and provides high precision

measurements. Does not extrapolate the CO<sub>2</sub>

CO<sub>2</sub>: 0-9999 ppm, temperature: -10 °C 4 years to 60 °C 14 °F to 140 °F, relative Comes with Android humidity: 0% to 85% atmospheric pressure: 0.3 to 1.1 atm (4.4 to 16.0 psi)

Detects the time the contact is either

opened or closed between two wired

Measures

CO<sub>2</sub>: 0-9999 ppm

contact points.

Measures

SIGNAL STRENGTH SENSORS - Aranet solutions for signal testing will allow you to find the best location for potential sensor placement with just a push of a button to immediately see the signal strength.

Radio Site Survey Ping-Pong Kit

RSSI sensor

9 years

Battery\*

8 years

Battery\*


IP68

IP class


IP class

\* Battery life up to...

The specifications or information contained in this document are subject to change without notice due to continuing introduction of design improvements. If there is any conflict between this document and compliance statements, the latter will supersede this document.



## ARANET WIRELESS ENVIRONMENTAL MONITORING SOLUTIONS



## Aranet.com

The specifications or information contained in this document are subject to change without notice due to continuing introduction of design improvements. If there is any conflict between this document and compliance statements, the latter will supersede this document.

For more detailed information about Aranet products, please visit **aranet.com**, contact your Aranet representative or write to **info@aranet.com**. Product specifications are subject to change without prior notice.

© 2022 SAF Tehnika, JSC. All rights reserved.