

# SCRAPER

## SCRAPEX ARGENTAX

ORDER NOW!

Order No.	46644.02
Knife size (L x W x H)	165 x 16.7 x 45 mm
Weight knife	81.0 g
Basic material	Plastic
Variations	46144.02



BLADE  
RETRACTABLE

**Blade protective cap**  
for safe transport

**Easy blade change**  
for efficient working

**Practical eyelet**  
for a secure attachment

**Large scraping  
width (36 mm)**  
for cleaning surfaces

**Rounded blade**  
to protect against damage  
and injuries

**Rounded ergonomic handle**  
for right and left handers

THE SAFER WAY TO CUT.

**martor**

# MARTOR SCRAPER SCRAPEX ARGENTAX


## TECHNICAL FEATURES

 Tool-less blade change	 Very abrasion resistant	 Ergonomic	 Scraper width (36 mm)
 For right and left handers	 Lanyard hole	 Protection cap	 Rounded-tip industrial blade
 Printable for promotional purposes			

## EXAMPLES OF USE



## MAIN CUTTING MATERIALS

 Self-adhesive label
--

## MOUNTABLE BLADES

	<b>REINFORCED RAZOR BLADE NO. 60044</b> 0.30 mm, rounded blade tips, 10 in magazine	<b>NO. 60044.50</b>
	<b>REINFORCED RAZOR BLADE NO. 44</b> 0.30 mm, 10 in magazine	<b>NO. 44.50</b>
	<b>REINFORCED RAZOR BLADE NO. 144</b> 0.25 mm, stainless, 10 in magazine	<b>NO. 144.50</b>

## PACKING INFORMATION

<b>Packaging unit</b>	1 in single unit box (10 scrapers in multipack)
<b>Size Single unit box</b>	180 x 20 x 49 mm
<b>Weight single unit box</b>	94.0 g
<b>EAN Code single unit box</b>	4002632803956
<b>Size outer pack</b>	108 x 104 x 185 mm
<b>Weight outer pack</b>	1020.0 g
<b>EAN Code outer pack</b>	4002632853951