

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0099990990

Status:


Active

Overview:

Mini-SPOX Wire-to-Board Connector System

Description:

2.50mm Pitch, Mini-SPOX PCB Header, Single Row, Vertical, Through Hole, Tin Plating, 6 Circuits, Bag, with Swaged PC Tails



Documents:	
2D Drawing (DXF)	Product Specification 52641001-PS-000 (PDF)
3D Model (PDF)	Product Specification PS-5264-001-001 (PDF)
2D Drawing DXF (PDF)	Packaging Specification SPK-5267-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	5267
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Mini-SPOX Wire-to-Board Connector System
Product Name	Mini-SPOX
Taxonomy	PCB Headers and Receptacles
UPC	800753577015
Physical	
Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	551.820/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5267 Series

Mates With

Mini-SPOX Receptacle Housing 5264

Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5267-06A-X
Reference - Drawing Numbers	
Packaging Specification	SPK-5267-001-001
Product Specification	52641001-PS-000, PS-5264-001-001
Sales Drawing	52670002-SD-000

This document was generated on 01/30/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION