

	Article description			Article-no./ GTIN	gurantee
<p><b>T.I.P.</b> Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt</p> <p>Tel.: 07263-9125-0 Fax: 07263-9125-25</p> <p>www.tip-pumpen.de</p>	Deep well pump BigWell 90/53 AUT			30084 4011458103843	24 months
	<b>Masterbox Informationen</b>				
	<b>Dimensions in cm</b>			<b>weight (kg) gross</b>	<b>Qty.</b>
	<b>Width</b>	<b>Depth</b>	<b>Heigth</b>		
	92,0	45,0	19,7	30,2	2
<b>Artikel Informationen</b>					
	<b>Dimensions in cm</b>			<b>weight (kg) net / gross</b>	<b>Qty.</b>
	<b>Width</b>	<b>Depth</b>	<b>Heigth</b>		
	90,5	21,6	17,0	13,8 / 14,6	1

## Deep well pump BigWell 90/53 AUT

### Description:

The deep well pump with stainless steel pump housing is a powerful energy-saving pump for pumping water from great depths. With the help of the integrated electronic control system, the pump switches on automatically. After closing the consumers, a switch-off takes place after reaching the maximum pressure. The pump is protected from damage due to dry running by the flow control system. Its small outer diameter of only 9.6 cm makes it ideal for use in narrow wells with a diameter of 10 cm or more. The expandable base protects against silting of the pump hydraulics and makes it sand-resistant for a sand content of 50 g/m<sup>3</sup> in the water. The pump has an integrated check valve, 23 m connection cable and a drain rope for optimal positioning.

### Technical Data:

motor:	900 Watt
max. head/pressure:	53 m / 5,3 bar
max. flow:	5.400 l/h
housing material:	Edelstahl
Max. grain size:	≤ 1 mm
Max. immersion depth:	20 m
Cable:	23 m / H07RN-F
Max. Temp. Medium:	35 °C
Pressure port:	30,93 mm (1" IG)
Min. well size:	100 mm
MEI	≥ 0,40

### Area of application:

For pumping water from great depths and transferring it at high pressure

### Approval marks:

