

Product: Wet Wipes

Specification 5*5 CM

Manufacture's: SHENZHEN NUOCHENGDA TECHNOLOGY
CO., LTD.

Address: NO107 Building T16 International Textile and
Apparel Raw material logistics Area of South
China City, No. 1 of Huanan Road, Pinghu Street,
Longgang District, Shenzhen, Guangdong, China

Compiled by (name+ signature) :



July Yan

(July Yan)

Approved by (+ signature) :

Ethan Chen

(Ethan Chen)



Material Safety Data Sheet

Report No.: STT20170209632R

Date: 2017-02-15

2 of 4

SECTION 1 - PRODUCT AND COMPANY IDENTIFICATION

Product Name: Wet Wipes

Color: White

Manufacture's/Supplier Name: SHENZHEN NUOCHENGDA TECHNOLOGY CO., LTD.

Address: NO107 Building T16 International Textile and Apparel Raw material logistics Area of South China City, No. 1 of Huanan Road, Pinghu Street, Longgang District, Shenzhen, Guangdong, China

Telephone number of the supplier: 0769-82557155

Fax.: 0769-82082508

E-mail address: 450799614@qq.com

SECTION 2 - COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Components	CAS#	%W/W
Polyester	--	95
Water	--	4
Ethyl alcohol	64-17-5	1

SECTION 3 - HAZARDS IDENTIFICATION

Color: White

This material is not classified as a hazardous substances.

SECTION 4 - FIRST AID MEASURES

Inhalation:

Remove patient from exposure. Keep patient at rest and give oxygen if breathing is difficult.

If symptoms develop, obtain medical attention.

Skin Contact:

After contact with skin, wash immediately with plenty of soap and water. In case of burns from hot material immediately cool affected skin as long as possible with cold water. Obtain medical attention and skin test to be done.

Eye Contact:

Remove particles by irrigating with eye wash solution or clean water, holding the eyelids part.

If symptoms persist, obtain medical attention.

Ingestion:

Unlikely to be hazardous if swallowed. Provided the patient is conscious, wash out mouth with water and give 200-300 ml of water to drink. Do not induce vomiting.

If symptoms develop, obtain medical attention.

SECTION 5 - FIRE FIGHTING MEASURES

Extinguishing Media:

As appropriate for surrounding fire. Extinguish preferably with foam, carbon dioxide or dry chemical.

Unsuitable Extinguishing Media:

Do not use jet or waterspray.

Shenzhen STONE Testing Technology Co., Ltd.

Address: East of F/4, Bldg. 11B, Area A, Tanglang Industrial Park, Taoyuan Street, Nanshan District, Shenzhen, Guangdong, China.

Tel: +86-755-36853890

Fax: +86-755-61640121



Material Safety Data Sheet

Report No.: STT20170209632R

Date: 2017-02-15

3 of 4

Fire Fighting Protective Equipment:

A self contained breathing apparatus and suitable protective clothing should be worn in fire conditions.

Hazardous Combustion Products:

Combustion or thermal decomposition will evolve toxic and irritant vapours.

Other:

Can melt and burn in a fire. Molten material tends to flow or drip and will propagate fire.

SECTION 6 - ACCIDENTAL RELEASE MEASURES

Personal Precautions:

Caution –spillages may be slippery . Ensure suitable personal (including respiratory protection) during removal of spillages. Dust clouds are sensitive to ignition by electrostatic discharge.

Environmental Exposure Controls:

Avoid release to the environment. Do not allow to enter drains, sewers or watercourses.

Methods for cleaning up:

Sweep up and shovel into waste drums or plastic bags.

SECTION 7 - HANDLING AND STORAGE

HANDLING:

Control dust formation. Do not eat, drink or smoke at the work place. Wash face and hands before Eating, drinking or smoking.

STORAGE:

Keep away from heat and direct sunlight .This product should be kept away from naked flames and other sources of ignition store at room temperature.

SECTION 8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

Provide adequate ventilation when the material and follow the principles of good occupational hygiene to control personal exposures.

SECTION 9 - PHYSICAL AND CHEMICAL PROPERTIES

Physical State/Form: Solid Non woven fabric

Color: White

odour: odourless

Decomposition Temperature (°C) : >300 (572°F)

Melting Point: 140-170 (284-338 °F)

Specific gravity: 0.85-0.95

Solubility: - Insoluble

SECTION 10 - STABILITY AND REACTIVITY

Chemical Stability:

stable under normal conditions.

Shenzhen STONE Testing Technology Co., Ltd.

Address: East of F/4, Bldg. 11B, Area A, Tanglang Industrial Park, Taoyuan Street, Nanshan District, Shenzhen, Guangdong, China.

Tel: +86-755-36853890

Fax: +86-755-61640121



Material Safety Data Sheet

Report No.: STT20170209632R

Date: 2017-02-15

4 of 4

Conditions to avoid:

Heat and direct sunlight.

Material to avoid :

Direct contact with open flames.

Hazardous Decomposition product:

Carbon monoxide, carbon dioxide, Hydrocarbon and Acrid smoke.

SECTION 11 ECOLOGICAL INFORMATION:

Environmental fate and distribution:

Insoluble in water. Floats on water. The product has low mobility in soil.

Persistence and Degradation:

The Product is non-biodegradable. Effort to reduce ,reuse or recycle waste conservation of energy and other resources.

SECTION 12 DISPOSAL CONSIDERATION

Regulatory Information:

Do not allow enter drains, sewers or watercourses.

Recommended:

Ref. to manufacture/supplier for information on recovery/recycling.

SECTION 13 TRANSPORTATION INFORMATION

NOT regulated by ICAO/IATA.

SECTION 14 OTHER REGULATORY INFORMATION

Not Classified as dangerous for supply/use.

SECTION 15 OTHER INFORMATION

Not applicable.

*** END OF REPORT ***