

SMART DOORBELL CAMERA

IP65 weather proof



DELTACO

SMART

PRODUCT DATA

Features:	Night vision, 2-way audio, and motion detection (100° angle).
Resolution:	1080p Full HD (1920x1080)
IR Nightvision:	5 m
Frame rate:	25 fps
View angle:	130°
Power:	Batteries or USB (USB power adapter included)
Batteries:	2x 18650 Li-ion (included), 6700 mAh
Standby time:	6 months
Storage:	MicroSD slot supporting up to 128 GB
Chime:	Not included, supports both mechanical and wireless 433 MHz
Wi-Fi Frequency:	2.4 GHz
Network protocol:	IEEE 802.11 b/g/n
Compatibility:	APP: DELTACO SMART HOME
Package contents:	Doorbell camera, Micro USB cable, USB power adapter, 2x 18650 batteries, screws, hex key and ejector pin and manual

IP65
WiFi
1080P Full HD
IR night vision



LOGISTICS DATA

Article number:	SH-DB02
Brand:	DELTACO
EAN Code:	7333048054586
Country of origin:	China
Custom tariff number:	85318040
Master carton packing unit:	20 pcs
Master carton gross weight:	9.4 kg
Master carton dimensions:	44.4 x 42.4 x 23.4 cm
Package type:	Box
Package weight:	0.44 kg
Package dimensions:	214 x 109 x 80 mm
Article weight:	235 g
Article dimensions:	136 x 50 x 33 mm

