

Brochure

VIAMI

OLP-35V2, OLP-35SC and OLP-38V2

SmartPocket™ V2 Broadband Power Meters

VIAMI Solutions new OLP-3xV2 Broadband Power Meters quickly, easily, and conveniently measure optical power levels and loss in fiber networks and fit perfectly in your pocket. Easy-to-use for technicians at any skill level SmartPocket V2 Broadband Power Meters (PM) complement VIAMI optical light sources (OLS) for insertion loss and continuity testing in both multimode and single-mode networks in all environments. They offer a dedicated and cost-optimized solution for testing and troubleshooting fiber in the field. The smart and rugged OLP-3xV2 also includes unprecedented data storage capacity supported by result downloads to a PC or upload to the cloud.



OLP-35V2

OLP-35SC



OLP-38V2

Key Benefits

- Ready when you need it – ultra-high reliability and high availability
 - Dependable, German design
 - Designed with outdoor environment in mind
 - Low power consumption for extended continuous use
 - Instant On – no boot time
- Easy to use
 - High-Visibility backlit graphical display with context-sensitive softkey
 - No setup 'OptiChek' measurement mode
 - Auto- λ , Multi- λ mode
 - Automatic upload of results via VIAMI Mobile Tech application

Key Features

- 1 nm incremental wavelength settings
- Universal optical interface supports all 2.5 mm with option for 1.25 mm connectors
- Fiber Tracing – detecting optical light source tone(s)
- Storage for > 1000 test results and PC download capability
- Bluetooth low energy connectivity to the VIAMI Mobile Tech App
- 3-year recalibration period

Applications

- Measuring optical power levels and link insertion loss for both Single mode and Multimode networks
- Network Build and Maintenance for
 - Enterprise/LAN
 - Access and Metro (LAN/WAN)
 - FTtx (e.g. Home/Antenna)
 - Standard and high-power level tests

Features and benefits

Ultra-reliable German design

Built for rugged, outdoor use
Still fits in your pocket!

Improved protection cap can be fully opened

Huge storage capacity

> 1000 test results

Softkey flexibility

Multiple power options (4-way)

2x Alkaline AA, 2x NiMH AA
rechargeable, AC power adapter, USB

Bluetooth low energy connectivity to the VIAVI Mobile Tech App

New high-visibility graphical display with backlight

Innovative low-power design exceptionally long battery life over 45 hrs. continuous operation

USB-C interface powering, offload of results, connection to PC



Products:

- The OLP-35V2 is the optimal device for standard telecommunication networks and multimode or single mode applications
- The OLP-35SC provides the same capabilities as the OLP-35V2 and comes with a fixed SC adapter
- The OLP-38V2 is a higher-power (up to +26 dBm) version for CATV HFC (with analog RF transmission) or amplified DWDM systems applications

Instant On – Easy to use – Good to go in no time

Instant on means SmartPocket V2 is ready as soon as you are, no waiting for an instrument to boot up, it's there the instant you need it. A high visibility back-lit display makes SmartPocket V2 usable in all lighting conditions indoors and outdoors, and combined with the super simple user navigation plus universal optical connector test port with OptiChek mode means you can close out more jobs per day.


OptiChek Mode

A broadband power meter that does not require wavelength configuration! Ideal for situations where you do not know the exact service wavelength in use or for a basic quick check to determine if a fiber is lit and power level is in the predicted/expected range. Just turn it on, connect, and take the measurement.*

* Increased uncertainty (to approximately +/- 1dB) is traded for speed and simplicity when you just want a quick confirmation of power with no thresholding, for Singlemode only: (1260nm to 1650nm)

Auto-λ, Multi-λ Mode

When SmartPocket V2 Broadband PMs are used in combination with SmartPocket V2 OLS, the new super-fast Auto-λ mode reduces the time to measure up to 3 wavelengths on the same fiber to less than a second. Delivering lightning-fast, error free, multi-λ loss testing saves time when testing and becomes critical to getting jobs finished and links delivered on time especially when working in high fiber-count environments. Plus, with a single button push results are saved and ready for upload to the cloud via the Mobile Tech App.



Robust and ready for field use

One of the key issues for optical field equipment is the risk of damage to the optical test port, this port has to be free of dirt and damage (e.g. scratches) in order to perform as required (according to specs). All it takes is a small piece of dust or dirt to be accidentally trapped and crushed when a fiber connection is made to damage the test port. The non-contact and easy clean approach with the SmartPocket V2 eliminates the risk of accidental test port damage and the integrated rubber 'bumpers' and test port cap make it ready for use in the real world and able to survive the odd bump or knock.

Superior Battery Life and powering options

Taking measurements and performing that certification of a fiber install is the final step to closing out tasks while you are still on-site. Without test equipment powered and ready to go you run the risk of missing a deadline or having to make a site re-visit to finish a job. To avoid this the SmartPocket V2 offers a low power consumption design for extended continuous use and supports 4 way powering with field replaceable NiMH rechargeable, off the shelf alkaline batteries, AC powering and power over USB. Meaning that you will never be short of power for long or have to wait for unit batteries to recharge.

Low Cost of Ownership

3 years calibration interval means no extra annual charges and your equipment will meet requirements for reporting and certifying (i.e. to be in calibration).

Test and Report Field Measurements

VIAMI Smart Reporter reporting software lets users quickly and efficiently download test results data from the power meter's memory with just a few clicks. After it's downloaded, the software reporting functions let users generate and customize professional certification reports.

VIAMI Report date: Thursday, January 14, 2021

Optichek Report - Sample 01

Technician Information

Company Name: Technician AG
Technician Name: Mr. Technician
Address: Technician Street
Postal Code: 72764
City: Reutlingen
State: Baden-Württemberg
Country: Germany
Phone: 0163438574
Email: technician@office.com

Device Type:	OLP355C/14	Calibration Date:	2021/JAN/12
Serial Number:	A-0443	Software Version:	2333V01.00.00

Measurement results

Fiber ID	λ (nm)	Power (dBm)	Power (μWatts)	Power (dB)	Reference (dBm)
2021-01-14T15:42:46	1310	-20.52			
2021-01-14T15:43:46	1310	-20.82			
2021-01-14T15:43:59	1310		11.22		
2021-01-14T15:45:01	1490			-19.80	0.00
Room-Q3, Fiber-001	1490			36.15	-56.37
Room-Q3, Fiber-002	1550	-22.86			
Room-Q3, Fiber-003	1550	-23.09			

Connected for superior workflow and reporting

In today's world it is essential for techs and their instruments to be connected, not only to reduce manual effort and risk of mistakes but also to deliver seamless reporting. SmartPocket V2 is integrated with the VIAMI Mobile Tech App to ensure optimal workflow freeing up techs and contractors to get on with their jobs rather than being slowed down with report generation and submission.

Job Manager

- Easily create job templates via Mobile Tech App
- Associate tests to specific workorder or job number
- Sequence of individual test tasks grouped together in a single job
- No need to type in settings or labels on the job site
- No more missed or invalid test results; launch, test and auto upload of results

Mobile Tech App


- Mobile App available for iOS and Android
- Independent guest account and integrated StrataSync™ account operation
- Create and push job with label list to instrument, pull test results back to app
- Enriches test results with workflow audit details, geolocation data and time stamp
- Synchronization to StrataSync for results upload, firmware updates, asset and option management



Job Manager and Mobile Tech App are part of the StrataSync Test Process Automation Suite, a solution that empowers you to deploy test plan procedures to technicians to simplify and automate your network tests. Test Accurately in Half the Time to Boost Productivity.

Inspect Before You Connect (IBYC)

Contamination is the number 1 reason for troubleshooting optical networks. Proactive inspection and cleaning of fiber connectors can prevent poor signal performance, equipment damage, and network downtime.



VIAVI Care Support Plans

Increase your productivity for up to 5 years with optional VIAVI Care Support Plans:

- Maximize your time with on-demand training, priority technical application support and rapid service.
- Maintain your equipment for peak performance at a low, predictable cost.

Plan availability depends on product and region. Not all plans are available for each product or in every region. To find out which VIAVI Care Support Plan options are available for this product in your region, contact your local representative or visit: viavisolutions.com/viavicareplan

Features

*5-year plans only

Plan	Objective	Technical Assistance	Factory Repair	Priority Service	Self-paced Training	5 Year Battery and Bag Coverage	Factory Calibration	Accessory Coverage	Express Loaner
 BronzeCare	Technician Efficiency	Premium	✓	✓	✓				
 SilverCare	Maintenance & Measurement Accuracy	Premium	✓	✓	✓	✓*	✓		
 MaxCare	High Availability	Premium	✓	✓	✓	✓*	✓	✓	✓



Contact Us **+1 844 GO VIAVI**
(+1 844 468 4284)

To reach the VIAVI office nearest you,
visit viavisolutions.com/contact

© 2021 VIAVI Solutions Inc.
Product specifications and descriptions in this document are subject to change without notice. Patented as described at viavisolutions.com/patents smartpocketv2-br-fop-nse-ae 30192953 902 0821