



Figure similar

Article No. : 1FL6054-2AF21-2AA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Engineering data	
Rated speed	3,000 rpm
Rated torque (100 K)	6.37 Nm
Rated current	11.6 A
Rated power	2.00 kW / 2.72 hp
Max. speed	5,000 rpm
Maximum torque	19.10 Nm
Max. current	34.8 A
Static torque	6.37 Nm
Moment of inertia	2.620 kgcm²

Physical constants	
Torque constant	0.55 Nm/A
Thermal class	B (130 °C)
Net weight	6.70 kg

Ambient conditions	
Ambient temperature	
Operation	0 ... 30 °C
Relative humidity	
Max. operation	90 % RH maximum (no condensation at 30 °C)

Standards	
Compliance with standards	CE, EAC

Mechanical data	
Motor type	Low Inertia
Motor type	Permanent-magnet synchronous motor
Shaft height	50
Encoder system	Incremental encoder TTL, 2500 S/R (13 bit)
Cooling	Natural cooling
Shaft end	Feather key
Radial runout tolerance	Class N
Vibration severity grade	Grade A
Degree of protection	IP65
Design acc. to Code I	IM B5 (IM V1, IM V3)
Connection type	Angular connector (rotatable)