

Data sheet for SIMOTICS S-1FK2

Article No. : 1FK2208-3AC11-1MA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar


Basic motor data	
Motor type	Permanent-magnet synchronous motor, Natural cooling, IP65
Motor type	Compact
Static torque	18.00 Nm
Static current	8.4 A
Maximum torque	51.00 Nm
Maximum current	29.5 A
Maximum speed	4,100 rpm
Rotor moment of inertia	32.6000 kgcm ²
Weight	14.6 kg

Rated data	
SINAMICS S210, 3AC 400V	
Rated speed	2,000 rpm
Rated torque	14.50 Nm
Rated current	7.0 A
Rated power	3.05 kW

Encoder system	
Encoder system	Encoder AM22DQC: Absolute encoder 22 bit + 12 bit multiturn

Motor connection	
Connection type	OCC for S210
Connector size	M23

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	80
Flange size (AB)	155 mm
Centering ring (N)	130 mm
Hole circle (M)	165 mm
Screw-on hole (S)	11.0 mm
Overall length (LB)	236 mm
Diameter of shaft (D)	32 mm
Length of shaft (E)	58 mm
Length of flange diagonal (P)	200 mm
Shaft end	Fitted key
Color of the housing	Standard (Anthracite, similar to RAL 7016)



Holding brake	
Holding torque	19.00 Nm
Average dynamic torque	12.00 Nm
Opening time	70 ms
Closing time	35 ms
Maximum single switching energy ¹⁾	2,000 J
Service life, operating energy	1,800,000 J
Holding current ²⁾	0.4 A
Break-induced current for 500 ms ²⁾	1.2 A

¹⁾Up to three consecutive emergency stops and up to 25% of all emergency stops as a Wmax high energy stop possible.
²⁾Typical value for 20°C ambient temperature. At -15°C the break-induced currents can be increased by up to 30%.