



communication module PROFINET High-Feature with integrated switch

Figure similar

product brand name	SIRIUS	
product category	Communication modules	
product designation	Communication module	
design of the product	PROFINET High Feature with integrated switch	
manufacturer's article number		
• of soft starter	3RW55	
General technical data		
reference code according to IEC 81346-2	A	
Substance Prohibition (Date)	02/11/2019	
Installation/ mounting/ dimensions		
mounting position	any	
fastening method	screw fixing	
height	126 mm	
width	28 mm	
depth	82 mm	
weight without packaging	0.1 kg	
Ambient conditions		
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog	
ambient temperature		
• during operation	-25 ... +60 °C; observe derating of basic unit above 40 °C	
• during storage and transport		
environmental category		
• during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6	
• during storage according to IEC 60721	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4	
• during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. height of fall 0.8 m)	
Safety related data		
protection class IP on the front according to IEC 60529	IP20	
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front	
Certificates/ approvals		
General Product Approval	For use in hazardous locations	Declaration of Conformity



[Confirmation](#)



[Explosion Protection Certificate](#)



Declaration of Conformity**Test Certificates**

[Type Test Certificates/Test Report](#)

Marine / Shipping**other**

[Confirmation](#)

[PROFINET-Certification](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5950-0CH00>

Cax online generator

<http://support.automation.siemens.com/WWW/CAXorder/default.aspx?lang=en&mlfb=3RW5950-0CH00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0CH00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5950-0CH00&lang=en

Characteristic: Tripping characteristics, I_t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0CH00/char>

Characteristic: Installation altitude

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5950-0CH00&objecttype=14&gridview=view1>

Simulation Tool for Soft Starters (STS)

<https://support.industry.siemens.com/cs/ww/en/view/101494917>



