



Rotary operating mechanism, actuating lever black, for encapsulated switches, for 63-125A, accessory for main and emergency off switch 3LD2 in molded-plastic enclosure and for repair and maintenance switch with EMC plate

Model	
product brand name	SETRON
product designation	Rotary operators
design of the product	accessories for 3LD2 main and EMERGENCY-STOP switches
degree of protection NEMA rating	1, 3R, 4X, 12
suitability for use	
• switch disconnecter	Yes
• circuit breaker	No
• EMERGENCY OFF switch	No
color	black
• of the actuating element	black
• Product component with axis	No
• Product component restart inhibit function block	No
• product component padlock locking mechanism	No
• product component key lock	No
accessories	
hasp thickness of the bracket locks	4 ... 8 mm
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD9284-1G>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3LD9284-1G>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3LD9284-1G](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD9284-1G)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

