



power contactor, AC-3e/AC-3, 12 A, 5.5 kW / 400 V, 3-pole, 24 V DC, 0.7-1.25\* Us, with integrated suppressor diode, auxiliary contacts: 1 NC, ring cable lug connection, size: S00, suitable for PLC outputs, not expandable with auxiliary switch

|                                                                                                              |                            |
|--------------------------------------------------------------------------------------------------------------|----------------------------|
| product brand name                                                                                           | SIRIUS                     |
| product designation                                                                                          | Coupling contactor         |
| product type designation                                                                                     | 3RT2                       |
| <b>General technical data</b>                                                                                |                            |
| size of contactor                                                                                            | S00                        |
| product extension                                                                                            |                            |
| • function module for communication                                                                          | No                         |
| • auxiliary switch                                                                                           | No                         |
| power loss [W] for rated value of the current                                                                |                            |
| • at AC in hot operating state                                                                               | 1.5 W                      |
| • at AC in hot operating state per pole                                                                      | 0.5 W                      |
| • without load current share typical                                                                         | 2.8 W                      |
| insulation voltage                                                                                           |                            |
| • of main circuit with degree of pollution 3 rated value                                                     | 690 V                      |
| • of auxiliary circuit with degree of pollution 3 rated value                                                | 690 V                      |
| surge voltage resistance                                                                                     |                            |
| • of main circuit rated value                                                                                | 6 kV                       |
| • of auxiliary circuit rated value                                                                           | 6 kV                       |
| maximum permissible voltage for protective separation between coil and main contacts according to EN 60947-1 | 400 V                      |
| shock resistance at rectangular impulse                                                                      |                            |
| • at DC                                                                                                      | 7.3g / 5 ms, 4.7g / 10 ms  |
| shock resistance with sine pulse                                                                             |                            |
| • at DC                                                                                                      | 11.4g / 5 ms, 7.3g / 10 ms |
| mechanical service life (operating cycles)                                                                   |                            |
| • of contactor typical                                                                                       | 30 000 000                 |
| • of the contactor with added electronically optimized auxiliary switch block typical                        | 5 000 000                  |
| • of the contactor with added auxiliary switch block typical                                                 | 10 000 000                 |
| reference code according to IEC 81346-2                                                                      | Q                          |
| Substance Prohibition (Date)                                                                                 | 10/01/2009                 |
| <b>Ambient conditions</b>                                                                                    |                            |
| installation altitude at height above sea level maximum                                                      | 2 000 m                    |
| ambient temperature                                                                                          |                            |
| • during operation                                                                                           | -25 ... +60 °C             |
| • during storage                                                                                             | -55 ... +80 °C             |
| relative humidity minimum                                                                                    | 10 %                       |
| relative humidity at 55 °C according to IEC 60068-2-30 maximum                                               | 95 %                       |
| <b>Main circuit</b>                                                                                          |                            |
| number of poles for main current circuit                                                                     | 3                          |

|                                                                        |                   |
|------------------------------------------------------------------------|-------------------|
| <b>number of NO contacts for main contacts</b>                         | 3                 |
| <b>operating voltage</b>                                               |                   |
| • at AC-3 rated value maximum                                          | 690 V             |
| • at AC-3e rated value maximum                                         | 690 V             |
| <b>operational current</b>                                             |                   |
| • at AC-1 at 400 V at ambient temperature 40 °C rated value            | 22 A              |
| • at AC-1                                                              |                   |
| — up to 690 V at ambient temperature 40 °C rated value                 | 22 A              |
| — up to 690 V at ambient temperature 60 °C rated value                 | 20 A              |
| • at AC-3                                                              |                   |
| — at 400 V rated value                                                 | 12 A              |
| — at 500 V rated value                                                 | 9.2 A             |
| — at 690 V rated value                                                 | 6.7 A             |
| • at AC-3e                                                             |                   |
| — at 400 V rated value                                                 | 12 A              |
| — at 500 V rated value                                                 | 9.2 A             |
| — at 690 V rated value                                                 | 6.7 A             |
| • at AC-4 at 400 V rated value                                         | 8.5 A             |
| • at AC-5a up to 690 V rated value                                     | 19.4 A            |
| • at AC-5b up to 400 V rated value                                     | 9.9 A             |
| • at AC-6a                                                             |                   |
| — up to 230 V for current peak value n=20 rated value                  | 7.2 A             |
| — up to 400 V for current peak value n=20 rated value                  | 7.2 A             |
| — up to 500 V for current peak value n=20 rated value                  | 7.2 A             |
| — up to 690 V for current peak value n=20 rated value                  | 6.7 A             |
| • at AC-6a                                                             |                   |
| — up to 230 V for current peak value n=30 rated value                  | 4.8 A             |
| — up to 400 V for current peak value n=30 rated value                  | 4.8 A             |
| — up to 500 V for current peak value n=30 rated value                  | 4.8 A             |
| — up to 690 V for current peak value n=30 rated value                  | 4.8 A             |
| minimum cross-section in main circuit at maximum AC-1 rated value      | 4 mm <sup>2</sup> |
| <b>operational current for approx. 200000 operating cycles at AC-4</b> |                   |
| • at 400 V rated value                                                 | 4.1 A             |
| • at 690 V rated value                                                 | 3.3 A             |
| <b>operational current</b>                                             |                   |
| • <b>at 1 current path at DC-1</b>                                     |                   |
| — at 24 V rated value                                                  | 20 A              |
| — at 60 V rated value                                                  | 20 A              |
| — at 110 V rated value                                                 | 2.1 A             |
| — at 220 V rated value                                                 | 0.8 A             |
| — at 440 V rated value                                                 | 0.6 A             |
| — at 600 V rated value                                                 | 0.6 A             |
| • <b>with 2 current paths in series at DC-1</b>                        |                   |
| — at 24 V rated value                                                  | 20 A              |
| — at 60 V rated value                                                  | 20 A              |
| — at 110 V rated value                                                 | 12 A              |
| — at 220 V rated value                                                 | 1.6 A             |
| — at 440 V rated value                                                 | 0.8 A             |
| — at 600 V rated value                                                 | 0.7 A             |
| • <b>with 3 current paths in series at DC-1</b>                        |                   |
| — at 24 V rated value                                                  | 20 A              |
| — at 60 V rated value                                                  | 20 A              |
| — at 110 V rated value                                                 | 20 A              |
| — at 220 V rated value                                                 | 20 A              |
| — at 440 V rated value                                                 | 1.3 A             |
| — at 600 V rated value                                                 | 1 A               |
| • <b>at 1 current path at DC-3 at DC-5</b>                             |                   |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                            |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>— at 24 V rated value</li> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> <li>● with 2 current paths in series at DC-3 at DC-5 <ul style="list-style-type: none"> <li>— at 24 V rated value</li> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> </ul> </li> <li>● with 3 current paths in series at DC-3 at DC-5 <ul style="list-style-type: none"> <li>— at 24 V rated value</li> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> <li>— at 220 V rated value</li> <li>— at 440 V rated value</li> <li>— at 600 V rated value</li> </ul> </li> </ul> | 20 A<br>0.5 A<br>0.15 A<br><br>20 A<br>5 A<br>0.35 A<br><br>20 A<br>20 A<br>20 A<br>1.5 A<br>0.2 A<br>0.2 A                                                                                                                                                                                                |
| <b>operating power</b> <ul style="list-style-type: none"> <li>● at AC-2 at 400 V rated value</li> <li>● at AC-3 <ul style="list-style-type: none"> <li>— at 230 V rated value</li> <li>— at 400 V rated value</li> <li>— at 500 V rated value</li> <li>— at 690 V rated value</li> </ul> </li> <li>● at AC-3e <ul style="list-style-type: none"> <li>— at 230 V rated value</li> <li>— at 400 V rated value</li> <li>— at 500 V rated value</li> <li>— at 690 V rated value</li> </ul> </li> </ul>                                                                                                                                         | 5.5 kW<br><br>3 kW<br>5.5 kW<br>5.5 kW<br>5.5 kW<br><br>3 kW<br>5.5 kW<br>5.5 kW<br>5.5 kW                                                                                                                                                                                                                 |
| <b>operating power for approx. 200000 operating cycles at AC-4</b> <ul style="list-style-type: none"> <li>● at 400 V rated value</li> <li>● at 690 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 2 kW<br>2.5 kW                                                                                                                                                                                                                                                                                             |
| <b>operating apparent power at AC-6a</b> <ul style="list-style-type: none"> <li>● up to 230 V for current peak value n=20 rated value</li> <li>● up to 400 V for current peak value n=20 rated value</li> <li>● up to 500 V for current peak value n=20 rated value</li> <li>● up to 690 V for current peak value n=20 rated value</li> </ul>                                                                                                                                                                                                                                                                                              | 2.8 kVA<br>4.9 kVA<br>6.2 kVA<br>8 kVA                                                                                                                                                                                                                                                                     |
| <b>operating apparent power at AC-6a</b> <ul style="list-style-type: none"> <li>● up to 230 V for current peak value n=30 rated value</li> <li>● up to 400 V for current peak value n=30 rated value</li> <li>● up to 500 V for current peak value n=30 rated value</li> <li>● up to 690 V for current peak value n=30 rated value</li> </ul>                                                                                                                                                                                                                                                                                              | 1.9 kVA<br>3.3 kVA<br>4.1 kVA<br>5.7 kVA                                                                                                                                                                                                                                                                   |
| <b>short-time withstand current in cold operating state up to 40 °C</b> <ul style="list-style-type: none"> <li>● limited to 1 s switching at zero current maximum</li> <li>● limited to 5 s switching at zero current maximum</li> <li>● limited to 10 s switching at zero current maximum</li> <li>● limited to 30 s switching at zero current maximum</li> <li>● limited to 60 s switching at zero current maximum</li> </ul>                                                                                                                                                                                                            | 200 A; Use minimum cross-section acc. to AC-1 rated value<br>123 A; Use minimum cross-section acc. to AC-1 rated value<br>96 A; Use minimum cross-section acc. to AC-1 rated value<br>74 A; Use minimum cross-section acc. to AC-1 rated value<br>61 A; Use minimum cross-section acc. to AC-1 rated value |
| <b>no-load switching frequency</b> <ul style="list-style-type: none"> <li>● at DC</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | 10 000 1/h                                                                                                                                                                                                                                                                                                 |
| <b>operating frequency</b> <ul style="list-style-type: none"> <li>● at AC-1 maximum</li> <li>● at AC-2 maximum</li> <li>● at AC-3 maximum</li> <li>● at AC-3e maximum</li> <li>● at AC-4 maximum</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                | 1 000 1/h<br>750 1/h<br>750 1/h<br>750 1/h<br>250 1/h                                                                                                                                                                                                                                                      |
| <b>Control circuit/ Control</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                            |
| <b>type of voltage of the control supply voltage</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | DC                                                                                                                                                                                                                                                                                                         |
| <b>control supply voltage at DC</b> <ul style="list-style-type: none"> <li>● rated value</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | 24 V                                                                                                                                                                                                                                                                                                       |
| <b>operating range factor control supply voltage rated value of magnet coil at DC</b> <ul style="list-style-type: none"> <li>● initial value</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 0.7                                                                                                                                                                                                                                                                                                        |

|                                                                    |                                                                                                                                      |
|--------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| • full-scale value                                                 | 1.25                                                                                                                                 |
| <b>design of the surge suppressor</b>                              | suppressor diode                                                                                                                     |
| <b>closing power of magnet coil at DC</b>                          | 2.8 W                                                                                                                                |
| <b>holding power of magnet coil at DC</b>                          | 2.8 W                                                                                                                                |
| <b>closing delay</b>                                               |                                                                                                                                      |
| • at DC                                                            | 25 ... 130 ms                                                                                                                        |
| <b>opening delay</b>                                               |                                                                                                                                      |
| • at DC                                                            | 7 ... 20 ms                                                                                                                          |
| <b>arcing time</b>                                                 | 10 ... 15 ms                                                                                                                         |
| <b>control version of the switch operating mechanism</b>           | Standard A1 - A2                                                                                                                     |
| <b>Auxiliary circuit</b>                                           |                                                                                                                                      |
| number of NC contacts for auxiliary contacts instantaneous contact | 1                                                                                                                                    |
| operational current at AC-12 maximum                               | 10 A                                                                                                                                 |
| <b>operational current at AC-15</b>                                |                                                                                                                                      |
| • at 230 V rated value                                             | 10 A                                                                                                                                 |
| • at 400 V rated value                                             | 3 A                                                                                                                                  |
| • at 500 V rated value                                             | 2 A                                                                                                                                  |
| • at 690 V rated value                                             | 1 A                                                                                                                                  |
| <b>operational current at DC-12</b>                                |                                                                                                                                      |
| • at 24 V rated value                                              | 10 A                                                                                                                                 |
| • at 48 V rated value                                              | 6 A                                                                                                                                  |
| • at 60 V rated value                                              | 6 A                                                                                                                                  |
| • at 110 V rated value                                             | 3 A                                                                                                                                  |
| • at 125 V rated value                                             | 2 A                                                                                                                                  |
| • at 220 V rated value                                             | 1 A                                                                                                                                  |
| • at 600 V rated value                                             | 0.15 A                                                                                                                               |
| <b>operational current at DC-13</b>                                |                                                                                                                                      |
| • at 24 V rated value                                              | 10 A                                                                                                                                 |
| • at 48 V rated value                                              | 2 A                                                                                                                                  |
| • at 60 V rated value                                              | 2 A                                                                                                                                  |
| • at 110 V rated value                                             | 1 A                                                                                                                                  |
| • at 125 V rated value                                             | 0.9 A                                                                                                                                |
| • at 220 V rated value                                             | 0.3 A                                                                                                                                |
| • at 600 V rated value                                             | 0.1 A                                                                                                                                |
| <b>contact reliability of auxiliary contacts</b>                   | 1 faulty switching per 100 million (17 V, 1 mA)                                                                                      |
| <b>UL/CSA ratings</b>                                              |                                                                                                                                      |
| <b>full-load current (FLA) for 3-phase AC motor</b>                |                                                                                                                                      |
| • at 480 V rated value                                             | 11 A                                                                                                                                 |
| • at 600 V rated value                                             | 11 A                                                                                                                                 |
| <b>yielded mechanical performance [hp]</b>                         |                                                                                                                                      |
| • for single-phase AC motor                                        |                                                                                                                                      |
| — at 110/120 V rated value                                         | 0.5 hp                                                                                                                               |
| — at 230 V rated value                                             | 2 hp                                                                                                                                 |
| • for 3-phase AC motor                                             |                                                                                                                                      |
| — at 200/208 V rated value                                         | 3 hp                                                                                                                                 |
| — at 220/230 V rated value                                         | 3 hp                                                                                                                                 |
| — at 460/480 V rated value                                         | 7.5 hp                                                                                                                               |
| — at 575/600 V rated value                                         | 10 hp                                                                                                                                |
| <b>contact rating of auxiliary contacts according to UL</b>        | A600 / Q600                                                                                                                          |
| <b>Short-circuit protection</b>                                    |                                                                                                                                      |
| <b>design of the fuse link</b>                                     |                                                                                                                                      |
| • for short-circuit protection of the main circuit                 |                                                                                                                                      |
| — with type of coordination 1 required                             | gG: 50A (690V,100kA), aM: 20A (690V,100kA), BS88: 35A (415V,80kA)                                                                    |
| — with type of assignment 2 required                               | gG: 20A (690V,100kA), aM: 16A (690V, 100kA), BS88: 20A (415V, 80kA)                                                                  |
| • for short-circuit protection of the auxiliary switch required    | gG: 10 A (500 V, 1 kA)                                                                                                               |
| <b>Installation/ mounting/ dimensions</b>                          |                                                                                                                                      |
| <b>mounting position</b>                                           | +/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface |
| <b>fastening method</b>                                            | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 60715                                                             |
| • side-by-side mounting                                            | Yes                                                                                                                                  |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|
| height                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 58 mm |
| width                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 45 mm |
| depth                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 73 mm |
| <b>required spacing</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |       |
| <ul style="list-style-type: none"> <li>• with side-by-side mounting <ul style="list-style-type: none"> <li>— forwards 10 mm</li> <li>— upwards 10 mm</li> <li>— downwards 10 mm</li> <li>— at the side 0 mm</li> </ul> </li> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards 10 mm</li> <li>— upwards 10 mm</li> <li>— at the side 6 mm</li> <li>— downwards 10 mm</li> </ul> </li> <li>• for live parts <ul style="list-style-type: none"> <li>— forwards 10 mm</li> <li>— upwards 10 mm</li> <li>— downwards 10 mm</li> <li>— at the side 6 mm</li> </ul> </li> </ul> |       |

#### Connections/ Terminals

|                                                                                                                                                                                                    |                                                                                                                     |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| <b>type of electrical connection</b>                                                                                                                                                               |                                                                                                                     |
| <ul style="list-style-type: none"> <li>• for main current circuit</li> <li>• for auxiliary and control circuit</li> <li>• at contactor for auxiliary contacts</li> <li>• of magnet coil</li> </ul> | Ring cable lug connection<br>ring terminal lug connection<br>Ring cable lug connection<br>Ring cable lug connection |

#### Safety related data

|                                                                                                                                                       |              |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| <b>product function</b>                                                                                                                               |              |
| <ul style="list-style-type: none"> <li>• mirror contact according to IEC 60947-4-1</li> </ul>                                                         | Yes          |
| B10 value with high demand rate according to SN 31920                                                                                                 | 1 000 000    |
| <b>proportion of dangerous failures</b>                                                                                                               |              |
| <ul style="list-style-type: none"> <li>• with low demand rate according to SN 31920</li> <li>• with high demand rate according to SN 31920</li> </ul> | 40 %<br>73 % |
| failure rate [FIT] with low demand rate according to SN 31920                                                                                         | 100 FIT      |
| T1 value for proof test interval or service life according to IEC 61508                                                                               | 20 a         |
| <b>protection class IP on the front according to IEC 60529</b>                                                                                        | IP00         |
| <b>suitability for use</b>                                                                                                                            |              |
| <ul style="list-style-type: none"> <li>• safety-related switching OFF</li> </ul>                                                                      | Yes          |

#### Certificates/ approvals

##### General Product Approval



[Confirmation](#)



[KC](#)



|     |                                              |                           |                   |                                                                                                |
|-----|----------------------------------------------|---------------------------|-------------------|------------------------------------------------------------------------------------------------|
| EMC | Functional Safety/Safety of Machinery        | Declaration of Conformity | Test Certificates |                                                                                                |
|     | <a href="#">Type Examination Certificate</a> |                           |                   | <a href="#">Special Test Certificate</a><br><a href="#">Type Test Certificates/Test Report</a> |

#### Marine / Shipping



|                   |       |         |                |             |
|-------------------|-------|---------|----------------|-------------|
| Marine / Shipping | other | Railway | Dangerous Good | Environment |
|-------------------|-------|---------|----------------|-------------|



[Confirmation](#)



[Vibration and Shock](#)

[Transport Information](#)

[Environmental Confirmations](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2017-4KB42>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2017-4KB42>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2017-4KB42>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)




[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RT2017-4KB42&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT2017-4KB42&lang=en)



Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2017-4KB42/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RT2017-4KB42&objecttype=14&gridview=view1>





last modified:

2/10/2023