



Position switch Metal enclosure Plain plunger Snap-action contacts 1 NO+1 NC
Short stroke, special operating travel Slow-action contacts 1 NO+2 NC Tappet
spring Actuating/restoring force 30 N customized

product brand name	SIRIUS
product designation	Mechanical position switches
product type designation	3SE5
manufacturer's article number	
• of the supplied actuator head for position switches	3SE5000-0AB01
• of the supplied switching contacts	on request
• of the supplied empty enclosure with cover	3SE5162-0AA00
suitability for use safety switch	Yes
General technical data	
product function positive opening	Yes
insulation voltage rated value	400 V
degree of pollution	class 3
surge voltage resistance rated value	6 kV
protection class IP	IP66/IP67
shock resistance	
• according to IEC 60068-2-27	30g / 11 ms
vibration resistance according to IEC 60068-2-6	0.35 mm/5g
mechanical service life (operating cycles) typical	5 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
thermal current	10 A
material of the enclosure of the switch head	plastic
reference code according to IEC 81346-2	B
continuous current of the C characteristic MCB	1 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A; for a short-circuit current smaller than 400 A
continuous current of the DIAZED fuse link gG	6 A
active principle	mechanical
repeat accuracy	0.05 mm
Substance Prohibitance (Date)	07/01/2006
minimum actuating force in directions of actuation	40 N
length of the sensor	125.3 mm
width of the sensor	56 mm
Ambient conditions	
ambient temperature	
• during operation	-25 ... +85 °C
• during storage	-40 ... +90 °C
explosion protection category for dust	none
design of the switching contact	mechanical
operating frequency rated value	50 ... 60 Hz
number of NC contacts for auxiliary contacts	3

number of NO contacts for auxiliary contacts	2	
operational current at AC-15		
• at 24 V rated value		
• at 125 V rated value		
• at 240 V rated value		
• at 400 V rated value		
operational current at DC-13		
• at 24 V rated value		
• at 125 V rated value		
• at 250 V rated value		
• at 400 V rated value		
Enclosure		
design of the housing	block, wide	
material of the enclosure	metal	
coating of the enclosure	cathodic dip coating	
design of the housing according to standard	No	
Drive Head		
design of the actuating element	Rounded plunger, high-grade steel plunger	
standard-compliant actuator head	EN 50041, design B	
shape of the switch head	rounded	
design of the switching function	positive opening	
circuit principle	snap-action contacts and slow-action contacts	
number of switching contacts safety-related	3	
cable entry type	3x (M20 x 1.5)	
Installation/ mounting/ dimensions		
mounting position	any	
fastening method	screw fixing	
Connections/ Terminals		
type of electrical connection	screw-type terminals	
type of connectable conductor cross-sections		
• solid		
• finely stranded with core end processing		
• for AWG cables solid		
• for AWG cables stranded		
design of the interface for safety-related communication	without	
Communication/ Protocol		
design of the interface	without	
Certificates/ approvals		
General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity



[Confirmation](#)



[Type Examination Certificate](#)



Test Certificates	other
-------------------	-------

[Type Test Certificates/Test Report](#)

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

<https://www.siemens.com/ic10>

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5162-0UB01-1AM4>

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5162-0UB01-1AM4>

<https://support.industry.siemens.com/cs/ww/en/ps/3SE5162-0UB01-1AM4>

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5162-0UB01-1AM4&lang=en



