



Figure similar

power relay, AC-3, 8.4 A, 4 kW / 400 V, 3-pole, 24 V AC, 45-450 Hz, auxiliary contacts: 1 NO, screw terminal, multi-unit packaging, pack = 50 units

|                                                                        |                                                |
|------------------------------------------------------------------------|------------------------------------------------|
| consumed active power                                                  | 4 W                                            |
| reference code according to IEC 81346-2                                | K                                              |
| Substance Prohibitance (Date)                                          | 07/01/2006                                     |
| ambient temperature during operation                                   | -25 ... +55 °C                                 |
| number of poles                                                        | 4                                              |
| number of NO contacts for main contacts                                | 3                                              |
| number of NC contacts for main contacts                                | 0                                              |
| type of voltage                                                        | AC                                             |
| operational current                                                    |                                                |
| • at AC-1 at 400 V rated value                                         | 20 A                                           |
| • at AC-3 at 400 V rated value                                         | 8.4 A                                          |
| • at AC-3e at 400 V rated value                                        | 6.4 A                                          |
| operating power                                                        |                                                |
| • at AC-3 at 400 V rated value                                         | 4 kW                                           |
| • at AC-3e at 400 V rated value                                        | 3 W                                            |
| control supply voltage at AC                                           |                                                |
| • at 50 Hz rated value                                                 | 24 ... 24 V                                    |
| • at 60 Hz rated value                                                 | 24 ... 24 V                                    |
| supply voltage frequency for auxiliary and control circuit rated value | 45 ... 450 Hz                                  |
| number of NC contacts for auxiliary contacts                           | 0                                              |
| number of NO contacts for auxiliary contacts                           | 1                                              |
| number of CO contacts for auxiliary contacts                           | 0                                              |
| fastening method                                                       | screw and snap-on mounting onto 35 mm DIN rail |
| • side-by-side mounting                                                | Yes                                            |
| height                                                                 | 62 mm                                          |
| width                                                                  | 36 mm                                          |
| depth                                                                  | 60 mm                                          |
| type of electrical connection                                          |                                                |
| • for main current circuit                                             | screw-type terminals                           |
| • for auxiliary and control circuit                                    | screw-type terminals                           |
| Safety related data                                                    |                                                |
| protection class IP on the front according to IEC 60529                | IP00                                           |
| Certificates/ approvals                                                |                                                |
| General Product Approval                                               | Declaration of Con-<br>formity                 |



[Confirmation](#)



| Declaration of Conformity | Test Certificates | other |
|---------------------------|-------------------|-------|
|---------------------------|-------------------|-------|



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

[Confirmation](#)



[Confirmation](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TG1010-0AC20-0AA0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TG1010-0AC20-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TG1010-0AC20-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3TG1010-0AC20-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TG1010-0AC20-0AA0&lang=en)


Characteristic: Tripping characteristics, I<sub>t</sub>, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3TG1010-0AC20-0AA0/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TG1010-0AC20-0AA0&objecttype=14&gridview=view1>





last modified:

11/21/2022 