



Figure similar

SITOP PSU200M/1-2AC/24VDC/5A/CO

SITOP PSU200M plus 5 A Stabilized power supply input: AC 120-230/230-500 V
output: 24 V DC/5 A Option for with protective varnish

Input	
type of the power supply network	1-phase and 2-phase AC
supply voltage at AC	
• initial value	Set by means of selector switch on the device; starting from $V_{in} > 90/180$ V
supply voltage	
• 1 at AC	120 ... 230 V
• 2 at AC	230 ... 500 V
input voltage	
• 1 at AC	85 ... 264 V
• 2 at AC	176 ... 550 V
design of input wide range input	Yes
overvoltage overload capability	1300 V _{peak} , 1.3 ms
operating condition of the mains buffering	at $V_{in} = 120/230$ V, typ. 150 ms at $V_{in} = 400$ V
buffering time for rated value of the output current in the event of power failure minimum	25 ms
operating condition of the mains buffering	at $V_{in} = 120/230$ V, typ. 150 ms at $V_{in} = 400$ V
line frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	2.2 A
• at rated input voltage 230 V	1.2 A
• at rated input voltage 500 V	0.61 A
current limitation of inrush current at 25 °C maximum	35 A
I ² t value maximum	1.7 A ² ·s
fuse protection type	T 3.15 A (not accessible)
• in the feeder	Recommended miniature circuit breaker at 1-phase operation: from 6 A (10 A) characteristic C (B); required at 2-phase operation: circuit breaker 2-pole connected or circuit breaker 3RV2011-1EA10 (setting 3.8 A) or 3RV2711-1ED10 (UL 489) at 230 V; 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489) at 400/500 V
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.1 %

residual ripple	
• maximum	50 mV
voltage peak	
• maximum	200 mV
adjustable output voltage	24 ... 28.8 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer
display version for normal operation	Green LED for 24 V OK
type of signal at output	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
behavior of the output voltage when switching on	Overshoot of V_{out} approx. 3 %
response delay maximum	1 s
voltage increase time of the output voltage	
• typical	50 ms
output current	
• rated value	5 A
• rated range	0 ... 5 A
supplied active power typical	120 W
short-term overload current	
• at short-circuit during operation typical	15 A
duration of overloading capability for excess current	
• at short-circuit during operation	25 ms
constant overload current	
• on short-circuiting during the start-up typical	6 A
product feature	
• bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	88 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	17 W
• during no-load operation maximum	4 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	3 %
setting time	
• load step 50 to 100% typical	2 ms
• load step 100 to 50% typical	2 ms
setting time	
• maximum	5 ms
Protection and monitoring	
design of the overvoltage protection	< 35 V
• typical	6 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 5.5 A or latching shutdown
enduring short circuit current RMS value	
• typical	6 A
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage U_{out} acc. to EN 60950-1 and EN 50178
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
• typical	0.25 mA
protection class IP	IP20
Approvals	
certificate of suitability	
• CE marking	Yes

<ul style="list-style-type: none"> • UL approval • CSA approval • cCSAus, Class 1, Division 2 • ATEX 	<p>Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259</p> <p>Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259</p> <p>No</p> <p>No</p>
<p>certificate of suitability</p> <ul style="list-style-type: none"> • IECEx • NEC Class 2 • ULhazloc approval • FM registration 	<p>No</p> <p>No</p> <p>No</p> <p>No</p>
type of certification CB-certificate	No
certificate of suitability	Yes
<ul style="list-style-type: none"> • EAC approval 	Yes
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS, DNV GL
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) 	<p>Yes</p> <p>No</p> <p>Yes</p> <p>No</p> <p>No</p>
EMC	
standard	
<ul style="list-style-type: none"> • for emitted interference • for mains harmonics limitation • for interference immunity 	<p>EN 55022 Class B</p> <p>EN 61000-3-2</p> <p>EN 61000-6-2</p>
environmental conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during transport • during storage 	<p>-25 ... +70 °C; with natural convection</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
Mechanics	
type of electrical connection	screw-type terminals
<ul style="list-style-type: none"> • at input • at output • for auxiliary contacts 	<p>L, N, PE: 1 screw terminal each for 0.2 ... 2.5 mm² single-core/finely stranded</p> <p>+, -: 2 screw terminals each for 0.2 ... 2.5 mm²</p> <p>13, 14 (alarm signal): 1 screw terminal each for 0.14 ... 1.5 mm²</p>
width of the enclosure	70 mm
height of the enclosure	125 mm
depth of the enclosure	121 mm
required spacing	
<ul style="list-style-type: none"> • top • bottom • left • right 	<p>50 mm</p> <p>50 mm</p> <p>0 mm</p> <p>0 mm</p>
net weight	0.6 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Buffer module
MTBF at 40 °C	1 123 973 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

