## **SIEMENS**

## **Data sheet**

## 6GK5923-0PS00-2RA3

product type designation

## SCALANCE PSR9230PoE power supply

SCALANCE PSR9230PoE 19" rack power-supply for power over Ethernet, Input: 230 V AC; output: 54 V DC.



type of current supply	180 W, input: 100 240 V AC, 50/60 Hz, output: 54 V / 4 A DC	
suitability for use	Power supply for PoE	
electrical data / input		
voltage curve / at input	AC single phase	
supply voltage / rated value	230 V	
supply voltage / rated value	85 264 V	
type of voltage / of the supply voltage	AC	
consumed current / at rated supply voltage / maximum	4 A	
design of input / wide range input	Yes	
overvoltage category	Category II	
buffering time / for rated value of the output current / in the event of power failure / minimum	20 ms	
line frequency		
• 50 Hz	Yes	
• 60 Hz	Yes	
• 1 / rated value	50 Hz	
2 / rated value	60 Hz	
line frequency	47 63 Hz	
input current / at rated input voltage 230 V / rated value	4 A	
current limitation / of inrush current / at 25 °C / maximum	25 A	
fuse protection type / at input	Fuse T 4A soldered in	
electrical data / output		
voltage curve / at output	linear falling (56V at 0A, 54V at 4A)	
output voltage / at DC / rated value	54 V	
display version / for normal operation	LED green for DC ok	
output current		
rated value	4 A	
rated range	0 4 A	
supplied active power / typical	180 W	
product feature / parallel switching of channels	Yes	
number of parallel-switched equipment resources / for increasing the power	2	
power loss [W]	275 W	
electrical data / closed-loop control		
relative overall tolerance / of the voltage	3 %	
electrical data / protection and monitoring		
design of the overvoltage protection / at output	< 60 V	
property of the output / short-circuit proof	Yes	
design of short-circuit protection	Electronic shutdown, automatic restart	

electrical data / safety	
galvanic isolation / between input and output	Yes
galvanic isolation	Input to output: 4 kV, input to PE 2.5 kV, output to PE: 2.25 kV
interfaces	
number of electrical connections	
<ul><li>for power supply</li></ul>	1
for signaling contact	0
type of electrical connection	
• for power supply	IEC plug
• at output	2-pole terminal block
signal inputs/outputs	
product component / signaling contact	No
design, dimensions and weights	
design	19-inch rack
width	446 mm
height	43.6 mm
depth	133 mm
net weight	2.8 kg
fastening method	
• 19-inch installation	Yes
<ul> <li>standard rail mounting</li> </ul>	Yes
ambient conditions	
ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +60 °C
<ul> <li>during storage</li> </ul>	-40 +60 °C
<ul> <li>during transport</li> </ul>	-40 +60 °C
• note	Convection
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP30
standards, specifications, approvals	
standard	
for safety / from CSA and UL	UL 62368-1:2014 (Second Edition) Report No. E115352, IEC 62368-1:2014 (Second Edition)
certificate of suitability	EN 61000-6-4: 2007
CE marking	Yes
• C-Tick	Yes
MTBF	110 a; at full load, 40 °C
reference temperature	40 °C
percental operating load	100 %
accessories	
accessories	Opposition asking asking a supplied asking to
• included	Connecting cable power supply / switch
further information / internet links	
internet link	h.W
to web page: selection aid TIA Selection Tool     to web site. Indicate a communication	http://www.siemens.com/snst
to website: Industrial communication     to website: Industry Mell	http://www.siemens.com/simatic-net
to website: Industry Mall     to website: Information and Download Contact	https://mail.industry.siemens.com
to website: Information and Download Center     to website: Image database	http://www.siemens.com/industry/infocenter
to website: Image database     to website: CAy Daymland Manager	http://automation.siemens.com/bilddb
to website: CAx-Download-Manager     to website: Industry Online Support	http://www.siemens.com/cax
to website: Industry Online Support	https://support.industry.siemens.com
last modified:	5/28/2023 🗗