Data sheet

6ES7193-6UP00-0DP2



SIMATIC ET 200SP, Potential distributor module, PotDis-BaseUnit PotDis-BU Typ P2, light-colored, 1 x P1-potential, 17 x P2-potential, Push-In terminals. P1-, P2- and AUX-rail diconnected from left BU, Packaging Unit: 1 Piece, WxH: 15mm x 117mm

| General information | |
|--|--|
| Product type designation | PotDis BU type P2, light version, PU 1 |
| HW functional status | FS10 and higher |
| Color code for module-specific color identification plate | CC63 |
| Supply voltage | |
| Rated value (DC) | |
| For P1 and P2 bus | 48 V; max. |
| for process terminals | 48 V; max. |
| external protection for power supply lines | Yes; 10 A miniature circuit breaker with type B or C tripping characteristic for the respective rated supply voltage |
| Current carrying capacity | |
| For P1 and P2 bus, max. | 10 A |
| For process terminals, max. | 10 A |
| Hardware configuration | |
| Formation of potential groups | |
| New potential group | No |
| Potential group continued from the left | Yes |
| Slots | |
| Number of slots | 1 |
| Potential separation | |
| between backplane bus and supply voltage | Yes |
| Isolation | |
| Isolation tested with | 3 250 V DC |
| Ambient conditions | |
| Ambient temperature during operation | |
| horizontal installation, min. | -30 °C |
| horizontal installation, max. | 60 °C |
| vertical installation, min. | -30 °C |
| vertical installation, max. | 50 °C |
| Altitude during operation relating to sea level | |
| Installation altitude above sea level, max. | 5 000 m; Restrictions for installation altitudes > 2 000 m, see manual |
| Accessories | |
| Color coding labels | |
| for process terminals | CC63 |
| connection method | |
| Terminals | |
| Terminal type | Push-in terminal |
| Conductor cross-section, min. | 0.14 mm² |
| Conductor cross-section, max. | 2.5 mm ² |
| Number of terminals with connection to P1 and P2 bus | 18; 17 terminals to P2, 1 terminal to P1 |

| Dimensions | |
|-----------------|--------|
| Width | 15 mm |
| Height | 117 mm |
| Depth | 35 mm |
| Weights | |
| Weight, approx. | 40 g |

last modified: 12/19/2020 🖸