



Figure similar

SIPLUS PSU300S 20 A

SIPLUS PS PSU300S 20 A based on 6EP1436-2BA10 with conformal coating, -40...+70 °C, stabilized power supply input: 400-500 V 3 AC output: 24 V DC/20 A

Input	
type of the power supply network	3-phase AC
supply voltage at AC	
<ul style="list-style-type: none"> <li>• minimum rated value</li> <li>• maximum rated value</li> <li>• initial value</li> <li>• full-scale value</li> </ul>	400 V 500 V 340 V 550 V
design of input wide range input	Yes
operating condition of the mains buffering	at $V_{in} = 400\text{ V}$
buffering time for rated value of the output current in the event of power failure minimum	6 ms
operating condition of the mains buffering	at $V_{in} = 400\text{ V}$
line frequency	
<ul style="list-style-type: none"> <li>• 1 rated value</li> <li>• 2 rated value</li> </ul>	50 Hz 60 Hz
line frequency	47 ... 63 Hz
input current	
<ul style="list-style-type: none"> <li>• at rated input voltage 400 V</li> <li>• at rated input voltage 500 V</li> </ul>	1.2 A 1 A
current limitation of inrush current at 25 °C maximum	36 A
I <sup>2</sup> t value maximum	0.9 A <sup>2</sup> ·s
fuse protection type	none
<ul style="list-style-type: none"> <li>• in the feeder</li> </ul>	Required: 3-pole connected miniature circuit breaker 6 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489-listed, DIVQ)
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
<ul style="list-style-type: none"> <li>• at output 1 at DC rated value</li> </ul>	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
<ul style="list-style-type: none"> <li>• on slow fluctuation of input voltage</li> <li>• on slow fluctuation of ohm loading</li> </ul>	0.5 % 1 %
residual ripple	
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	150 mV
voltage peak	
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	240 mV
adjustable output voltage	24 ... 28 V
product function output voltage adjustable	Yes

type of output voltage setting	via potentiometer; max. 480 W
display version for normal operation	Green LED for 24 V OK
type of signal at output	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	1.5 s
voltage increase time of the output voltage	
• typical	30 ms
• maximum	500 ms
output current	
• rated value	20 A
• rated range	0 ... 20 A
supplied active power typical	480 W
short-term overload current	
• on short-circuiting during the start-up typical	35 A
• at short-circuit during operation typical	35 A
duration of overloading capability for excess current	
• on short-circuiting during the start-up	100 ms
• at short-circuit during operation	100 ms
product feature	
• bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
<b>Efficiency</b>	
efficiency in percent	91 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	47 W
<b>Closed-loop control</b>	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	3 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	3 %
setting time	
• load step 50 to 100% typical	2 ms
• load step 100 to 50% typical	2 ms
setting time	
• maximum	10 ms
<b>Protection and monitoring</b>	
design of the overvoltage protection	protection against overvoltage in case of internal fault Vout < 35 V
• typical	25.5 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
enduring short circuit current RMS value	
• maximum	7 A
overcurrent overload capability in normal operation	overload capability 150 % Iout rated up to 5 s/min
<b>Safety</b>	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra-low output voltage Uout acc. to EN 60950-1 and EN 50178, transformer acc. to EN 61558-2-16
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
• typical	1 mA
protection class IP	IP20
<b>Approvals</b>	
certificate of suitability	
• CE marking	Yes
<b>EMC</b>	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2

environmental conditions	
ambient temperature <ul style="list-style-type: none"> <li>• in horizontal mounting position during operation</li> <li>• during storage and transport</li> </ul>	-40 ... +60 °C; with natural convection -40 ... +85 °C
installation altitude at height above sea level maximum	6 000 m
ambient condition relating to ambient temperature - air pressure - installation altitude	In case of operation at altitudes of 2000 - 6000 m above sea level: Output power derating of -7.5 %/1000 m or reduction of the ambient temperature by 5 K/1000 m
relative humidity with condensation according to IEC 60068-2-38 maximum	100 %; RH incl. condensation/frost (no commissioning if condensation is present), horizontal installation
chemical resistance to commercially available cooling lubricants	Yes; incl. diesel and oil droplets in the air
resistance to biologically active substances conformity according to EN 60721-3-3	Yes; Class 3B2 mold, fungal, sponge spores (except fauna); class 3B3 upon request
resistance to chemically active substances conformity according to EN 60721-3-3	Yes; Class 3C4 (RH < 75%) incl. salt spray acc. to EN 60068-2-52 (severity level 3)
resistance to mechanically active substances conformity according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust
resistance to biologically active substances conformity according to EN 60721-3-6	Yes; Class 6B2 mold, fungal, sponge spores (except fauna)
resistance to chemically active substances conformity according to EN 60721-3-6	Yes; Class 6C3 (RH < 75%) incl. salt spray acc. to EN 60068-2-52 (severity level 3)
resistance to mechanically active substances conformity according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust
coating for equipped printed circuit board according to EN 61086	Yes; Class 2 for high availability
type of coating protection against pollution according to EN 60664-3	Yes; Type 1 protection
type of test of the coating according to MIL-I-46058C	Yes; Discoloration of the coating during service life possible
product conformity of the coating Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal Coating, Class A
Mechanics	
type of electrical connection <ul style="list-style-type: none"> <li>• at input</li> <li>• at output</li> <li>• for auxiliary contacts</li> </ul>	screw-type terminals L1, L2, L3, PE: 1 screw terminal each for 0.5 ... 4 mm <sup>2</sup> single-core/finely stranded +, -: 2 screw terminals each for 0.2 ... 4 mm <sup>2</sup> 13, 14 (alarm signal): 1 screw terminal each for 0.05 ... 2.5 mm <sup>2</sup>
width of the enclosure	90 mm
height of the enclosure	145 mm
depth of the enclosure	150 mm
required spacing <ul style="list-style-type: none"> <li>• top</li> <li>• bottom</li> <li>• left</li> <li>• right</li> </ul>	40 mm 40 mm 0 mm 0 mm
net weight	1.6 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Redundancy module, buffer module, selectivity module, DC UPS
mechanical accessories	Device identification label 20 mm × 7 mm, pale turquoise 3RT1900-1SB20
MTBF at 40 °C	500 000 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

