



Figure similar

SITOP PSU6200/1AC/DC24V/10A/EX

SITOP PSU6200 Ex 24 V/10 A stabilized power supply input: 120/230 V AC output: 24 V / 10 A DC with diagnostic interface with painted printed circuit boards

Input	
type of the power supply network	1-phase AC or DC
supply voltage at AC	
• minimum rated value	120 V
• maximum rated value	240 V
• initial value	85 V
• full-scale value	264 V
supply voltage	
• at DC	110 ... 240 V
input voltage	
• at DC	85 ... 275 V
design of input wide range input	Yes
overvoltage overload capability	300 V AC for 30 s
operating condition of the mains buffering	at $V_{in} = 240 V$
buffering time for rated value of the output current in the event of power failure minimum	45 ms
operating condition of the mains buffering	at $V_{in} = 240 V$
line frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	2.2 A
• at rated input voltage 240 V	1.2 A
current limitation of inrush current at 25 °C maximum	6 A
fuse protection type	5 A
• in the feeder	Circuit breaker from 4 A characteristic C/6 A characteristic B to 10 A characteristic C or circuit breaker 3RV2011-1EA10 (setting 4 A) or 3RV2711-1ED10 (UL 489)
Output	
voltage curve at output	Controlled, isolated DC voltage
number of outputs	1
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.1 %
residual ripple	

<ul style="list-style-type: none"> <li>• maximum</li> <li>• typical</li> </ul>	<p>30 mV</p> <p>20 mV</p>
voltage peak	
<ul style="list-style-type: none"> <li>• maximum</li> <li>• typical</li> </ul>	<p>30 mV</p> <p>20 mV</p>
adjustable output voltage	24 ... 28 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer; max. 240 W (288 W up to 45°C)
display version for normal operation	Green LED for 24 V OK
type of signal at output	Electronic contact (NO contact, contact rating 30 V DC/0.1 A) for DC O.K. or diagnostic interface
behavior of the output voltage when switching on	Overshoot of $V_{out} < 2\%$
response delay maximum	0.5 s
voltage increase time of the output voltage	
<ul style="list-style-type: none"> <li>• typical</li> </ul>	200 ms
output current	
<ul style="list-style-type: none"> <li>• rated value</li> <li>• rated range</li> </ul>	<p>10 A</p> <p>0 ... 10 A; 12 A up to +45°C; +60 ... +70 °C: Derating 3%/K</p>
supplied active power typical	240 W
short-term overload current	
<ul style="list-style-type: none"> <li>• on short-circuiting during the start-up typical</li> <li>• at short-circuit during operation typical</li> </ul>	<p>12 A</p> <p>12 A</p>
product feature	
<ul style="list-style-type: none"> <li>• parallel switching of outputs</li> <li>• bridging of equipment</li> </ul>	<p>can be set with DIP switch</p> <p>Yes; switchable characteristic</p>
number of parallel-switched equipment resources for increasing the power	2
<b>Efficiency</b>	
efficiency in percent	92.8 %
power loss [W]	
<ul style="list-style-type: none"> <li>• at rated output voltage for rated value of the output current typical</li> <li>• during no-load operation maximum</li> </ul>	<p>18 W</p> <p>2.2 W</p>
<b>Closed-loop control</b>	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
<ul style="list-style-type: none"> <li>• load step 10 to 90% typical</li> <li>• load step 90 to 10% typical</li> <li>• maximum</li> </ul>	<p>2 ms</p> <p>2 ms</p> <p>3 ms</p>
<b>Protection and monitoring</b>	
design of the overvoltage protection	< 32 V
<ul style="list-style-type: none"> <li>• typical</li> </ul>	12 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
overcurrent overload capability in normal operation	overload capability 150 % I <sub>out</sub> rated up to 5 s/min
<b>Safety</b>	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra low output voltage $V_{out}$ according to EN 60950-1
operating resource protection class	Class I
leakage current	
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	3.5 mA
protection class IP	IP20
<b>Approvals</b>	
certificate of suitability	
<ul style="list-style-type: none"> <li>• CE marking</li> <li>• UL approval</li> <li>• CSA approval</li> <li>• cCSAus, Class 1, Division 2</li> <li>• ATEX</li> </ul>	<p>Yes</p> <p>Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)</p> <p>Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)</p> <p>No</p> <p>Yes; ATEX (EX) II 3G Ex ec nC IIC T3 Gc</p>

certificate of suitability <ul style="list-style-type: none"> <li>• relating to ATEX</li> <li>• IECEx</li> <li>• NEC Class 2</li> <li>• ULhazloc approval</li> <li>• FM registration</li> </ul>	IECEX Ex ec nC IIC T3 Gc; ATEX (EX) II 3G Ex ec nC IIC T3 Gc Yes; IECEx Ex ec nC IIC T3 Gc No No No
certificate of suitability shipbuilding approval	Yes
shipbuilding approval	ABS; in process: DNV
Marine classification association <ul style="list-style-type: none"> <li>• American Bureau of Shipping Europe Ltd. (ABS)</li> <li>• French marine classification society (BV)</li> <li>• DNV GL</li> <li>• Lloyds Register of Shipping (LRS)</li> <li>• Nippon Kaiji Kyokai (NK)</li> </ul>	Yes No No No No
<b>EMC</b>	
standard <ul style="list-style-type: none"> <li>• for emitted interference</li> <li>• for mains harmonics limitation</li> <li>• for interference immunity</li> </ul>	EN 55022 Class B EN 61000-3-2 EN 61000-6-2
<b>environmental conditions</b>	
ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during transport</li> <li>• during storage</li> </ul>	-30 ... +70 °C; with natural convection a monotonically increasing start-up from -25 °C, safe start-up from -40 °C -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
<b>Mechanics</b>	
type of electrical connection <ul style="list-style-type: none"> <li>• at input</li> <li>• at output</li> <li>• for auxiliary contacts</li> </ul>	push-in terminals L1/+, L2/N/-, PE: push-in for 0.5 ... 4 mm <sup>2</sup> single-core/finely stranded +1, +2, -1, -2, -3: push-in for 0.5 ... 2.5 mm <sup>2</sup> 13, 14 (alarm signal): 1 push-in terminal each for 0.2 ... 1.5 mm <sup>2</sup>
width of the enclosure	45 mm
height of the enclosure	135 mm
depth of the enclosure	125 mm
required spacing <ul style="list-style-type: none"> <li>• top</li> <li>• bottom</li> <li>• left</li> <li>• right</li> </ul>	45 mm 45 mm 0 mm 0 mm
net weight	0.9 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Buffer module, redundancy module
mechanical accessories	Identification labels SIMATIC ET 200SP 6ES7193-6LF30-0AW0
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

