




current transformer 3000/5 A 30 VA CL 1.0

Model			
product brand name		SENTRON	
product designation		Current transformer	
design of the product		Bushing-type current transformers	
operating apparent power rated value		30 VA	
Protection class			
protection class IP		IP20	
Connections			
type of electrical connection at output		screw-type terminals	
Mechanical Design			
height		127.5 mm	
height of the opening		36 mm	
width		112 mm	
width of the push-through bus bar at 1 bus bar maximum		64 mm	
width of the push-through bus bar in case of 2 bus bars maximum		51 mm	
depth		77 mm	
fastening method		screw fixing	
diameter of inlet opening		41 mm	
outer diameter of the push-through conductor maximum		41 mm	
net weight		1 157 g	
Environmental conditions			
ambient temperature during operation			
• minimum			
• maximum			
		-30 °C	
		55 °C	
Certificates			
reference code according to EN 61346-2		T	
General Product Approval		Declaration of Conformity	
		other	

[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4NC5441-2CN21>

Service & Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4NC5441-2CN21>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4NC5441-2CN21

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

12/20/2020

