



Figure similar

SIPLUS ET 200SP CP 1543SP-1 ISEC based on 6GK7543-6WX00-0XE0 with conformal coating, -40...+70 °C, security (firewall and VPN) open IE communication (TCP/IP, ISO-on-TCP, UDP) PG/OP, S7 routing, IP broadcast/multicast, SNMPV1/V3, DHCP, secure email, IPv4/IPv6, support of SINEMA Remote Connect with autoconfiguration, time synchronization via NTP, access to web server of CPU, BusAdapter required

transfer rate	
transfer rate	
<ul style="list-style-type: none"> at the 1st interface 	10 ... 100 Mbit/s
interfaces	
number of interfaces / according to Industrial Ethernet	1
number of electrical connections	
<ul style="list-style-type: none"> at the 1st interface / according to Industrial Ethernet 	2
type of electrical connection	
<ul style="list-style-type: none"> at the 1st interface / according to Industrial Ethernet 	via ET 200SP bus adapter (RJ45, FC, SCRJ), integrated switch
supply voltage, current consumption, power loss	
type of voltage / of the supply voltage	DC
supply voltage	24 V
supply voltage	19.2 ... 28.8 V
power loss [W]	6 W
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> for vertical installation / during operation for horizontally arranged busbars / during operation during storage during transport 	-40 ... +50 °C -40 ... +70 °C -40 ... +70 °C -40 ... +70 °C
installation altitude / at height above sea level / maximum	5000 m
ambient condition / relating to ambient temperature - air pressure - installation altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax - 20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
relative humidity	
<ul style="list-style-type: none"> with condensation / according to IEC 60068-2-38 / maximum 	100 %; RH including condensation/frost (no commissioning when condensation is present), horizontal installation
chemical resistance / to commercially available cooling lubricants	Yes; incl. airborne diesel and oil droplets
resistance to biologically active substances	
<ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3B2 mold and fungal spores (excluding fauna), Class 3B3 on request Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
resistance to chemically active substances	
<ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3C4 (RH < 75 %) incl. salt spray in accordance with EN 60068-2-52 (Severity 3). The supplied plug covers must remain in place on the unused interfaces during operation. Yes
resistance to mechanically active substances	
<ul style="list-style-type: none"> conformity according to EN 60721-3-3 	Yes; Class 3S4 incl. sand, dust. The supplied plug covers must remain in place over the unused interfaces during operation.

<ul style="list-style-type: none"> conformity according to EN 60721-3-6 	Yes; Class 6S3 incl. sand, dust. The supplied plug covers must remain in place over the unused interfaces during operation.
coating / for equipped printed circuit board / according to EN 61086	Yes; Class 2 for high availability
type of coating / protection against pollution according to EN 60664-3	Yes; Protection of the type 1
type of test / of the coating / according to MIL-I-46058C	Yes; Coating discoloration during service life possible
product conformity / of the coating / Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal coating, class A
protection class IP	IP20
design, dimensions and weights	
width	60 mm
height	117 mm
depth	74 mm
net weight	0.18 kg
fastening method <ul style="list-style-type: none"> 35 mm top hat DIN rail mounting 	Yes
product features, product functions, product components / general	
number of units <ul style="list-style-type: none"> per CPU / maximum note 	2 2 CPs can be plugged in per CPU, simultaneous operation with BA Send and CM DP is possible
performance data / open communication	
number of possible connections / for open communication <ul style="list-style-type: none"> by means of T blocks / maximum 	32
data volume <ul style="list-style-type: none"> as user data per ISO on TCP connection / for open communication / by means of T blocks / maximum 	65536 byte
performance data / S7 communication	
number of possible connections / for S7 communication <ul style="list-style-type: none"> maximum with OP connections / maximum 	16 16
performance data / multi-protocol mode	
number of active connections / with multi-protocol mode	32
performance data / IT functions	
number of possible connections <ul style="list-style-type: none"> as email client / maximum 	1
product functions / management, configuration, engineering	
product function / MIB support	Yes
protocol / is supported <ul style="list-style-type: none"> SNMP v1 SNMP v3 DCP LLDP 	Yes Yes Yes Yes
configuration software <ul style="list-style-type: none"> required 	STEP 7 Professional V14 (TIA Portal) or higher
identification & maintenance function <ul style="list-style-type: none"> I&M0 - device-specific information I&M1 - higher level designation/location designation 	Yes Yes
product functions / diagnostics	
product function / web-based diagnostics	Yes; via ET 200SP CPU
product functions / security	
firewall version	stateful inspection
product function / with VPN connection	IPsec, SINEMA RC
type of encryption algorithms / with VPN connection	AES-256, AES-192, AES-128, 3DES-168, DES-56
type of authentication procedure / with VPN connection	Preshared key (PSK), X.509v3 certificates
type of hashing algorithms / with VPN connection	MD5, SHA-1
number of possible connections / with VPN connection	4
product function <ul style="list-style-type: none"> switch-off of non-required services blocking of communication via physical ports 	Yes Yes

<ul style="list-style-type: none"> • log file for unauthorized access 	Yes
product functions / time	
product function / SICLOCK support	Yes
product function / pass on time synchronization	No
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • NTP (secure) 	Yes
time synchronization	
<ul style="list-style-type: none"> • from NTP-server 	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/snst
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity . To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com . (V3.4)

last modified:

7/7/2022 