



Figure similar

SIPLUS ET 200SP CM CAN based on 6ES7137-6EA00-0BA0 with conformal coating, -40...+60 °C, gateway to CAN Bus or CANopen networks, CAN 2.0A/B, CANopen Manager to CiA301/302, CANopen Slave to CiA301/302, IP20

General information	
Product type designation	CM 1x CAN ST
Firmware version	
<ul style="list-style-type: none"> FW update possible 	Yes
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> Module swapping during operation (hot swapping) 	Yes
<ul style="list-style-type: none"> Isochronous mode 	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, typ.	20 mA
Current consumption, max.	25 mA
Power loss	
Power loss, typ.	0.5 W
Address area	
Address space per module	
<ul style="list-style-type: none"> Address space per module, max. 	256 byte
1. Interface	
Interface type	CAN according to CiA 303-1
Isolated	Yes; 500 V AC or 707 V DC
Interface types	
<ul style="list-style-type: none"> Number of ports 	1
<ul style="list-style-type: none"> Design of the connection 	Push-in terminal
CAN	
<ul style="list-style-type: none"> CAN operating modes 	CAN Standard CAN 2.0A/B; CANopen Manager / Slave acc. to CiA
<ul style="list-style-type: none"> Specification acc. to CiA 	CiA 301 & CiA 302
<ul style="list-style-type: none"> Transmission rate, min. 	10 kbit/s
<ul style="list-style-type: none"> Transmission rate, max. 	1 000 kbit/s
<ul style="list-style-type: none"> Number of slaves, max. 	60
<ul style="list-style-type: none"> Number of SDOs in parallel 	16; Parallel
<ul style="list-style-type: none"> Number of PDOs 	128; Send / receive
Services	
— Node/life-guarding	Yes

— Heartbeat	Yes
— SYNC	Yes
Interrupts/diagnostics/status information	
Alarms	Yes
Diagnostics function	Yes
Diagnostics indication LED	
• RUN LED	Yes
• ERROR LED	Yes
• MAINT LED	No
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
Potential separation	
between backplane bus and interface	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
CE mark	Yes
RoHS conformity	Yes
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-40 °C; = Tmin (incl. condensation/frost)
• horizontal installation, max.	60 °C; = Tmax; +70 °C with configured empty slots to the left and right of the module
• vertical installation, min.	-40 °C; = Tmin
• vertical installation, max.	50 °C; = Tmax
• ceiling installation, min.	-40 °C; = Tmin
• ceiling installation, max.	50 °C; = Tmax
• floor installation, min.	-40 °C; = Tmin
• floor installation, max.	50 °C; = Tmax
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
Relative humidity	
• With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
Resistance	
Coolants and lubricants	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
— Against mechanical environmental conditions acc. to EN 60721-3-3	Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)
Use on ships/at sea	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
— to chemically active substances according to EN 60721-3-6	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *
— Against mechanical environmental conditions acc. to EN 60721-3-6	Yes; Class 6M4 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)
Usage in industrial process technology	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
Remark	

— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04

* The supplied plug covers must remain in place over the unused interfaces during operation!

Conformal coating	
<ul style="list-style-type: none">• Coatings for printed circuit board assemblies acc. to EN 61086• Protection against fouling acc. to EN 60664-3• Military testing according to MIL-I-46058C, Amendment 7• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Class 2 for high reliability Yes; Type 1 protection Yes; Discoloration of coating possible during service life Yes; Conformal coating, Class A
Decentralized operation	
to SIMATIC S7-300	No
to SIMATIC S7-400	No
to SIMATIC S7-1200	Yes
to SIMATIC S7-1500	Yes
Dimensions	
Width	15 mm
Height	73 mm
Depth	58 mm
Weights	
Weight, approx.	32 g

last modified:

8/3/2022 