



SIMATIC S7-1500, analog input module AI 16xU BA, 16-bit resolution accuracy 0.5%, 16 channels in groups of 16, common mode voltage 4 V DC, diagnostics, hardware interrupts; delivery including infeed element, shield bracket and shield terminal: front connector (screw terminals or push-in) to be ordered separately

General information	
Product type designation	AI 16xU BA
HW functional status	From FS01
Firmware version	V1.0.0
<ul style="list-style-type: none"> <li>FW update possible</li> </ul>	Yes
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> <li>Isochronous mode</li> </ul>	No
<ul style="list-style-type: none"> <li>Prioritized startup</li> </ul>	No
<ul style="list-style-type: none"> <li>Measuring range scalable</li> </ul>	No
<ul style="list-style-type: none"> <li>Scalable measured values</li> </ul>	No
<ul style="list-style-type: none"> <li>Adjustment of measuring range</li> </ul>	No
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	V16 with HSP 312 / V17
<ul style="list-style-type: none"> <li>STEP 7 configurable/integrated from version</li> </ul>	V5.5 SP3 / -
<ul style="list-style-type: none"> <li>PROFIBUS from GSD version/GSD revision</li> </ul>	V1.0 / V5.1
<ul style="list-style-type: none"> <li>PROFINET from GSD version/GSD revision</li> </ul>	V2.3 / -
Operating mode	
<ul style="list-style-type: none"> <li>Oversampling</li> </ul>	No
<ul style="list-style-type: none"> <li>MSI</li> </ul>	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	No
Power	
Power available from the backplane bus	0.85 W
Power loss	
Power loss, typ.	0.75 W
Analog inputs	
Number of analog inputs	16
<ul style="list-style-type: none"> <li>For voltage measurement</li> </ul>	16
permissible input voltage for voltage input (destruction limit), max.	12 V; 12 V continuous, 30 V for max. 1 s
Input ranges (rated values), voltages	
<ul style="list-style-type: none"> <li>0 to +5 V</li> </ul>	No
<ul style="list-style-type: none"> <li>0 to +10 V</li> </ul>	No
<ul style="list-style-type: none"> <li>1 V to 5 V</li> </ul>	Yes
<ul style="list-style-type: none"> <li>— Input resistance (1 V to 5 V)</li> </ul>	10 MΩ
<ul style="list-style-type: none"> <li>-1 V to +1 V</li> </ul>	Yes
<ul style="list-style-type: none"> <li>— Input resistance (-1 V to +1 V)</li> </ul>	10 MΩ
<ul style="list-style-type: none"> <li>-10 V to +10 V</li> </ul>	Yes

— Input resistance (-10 V to +10 V)	10 MΩ
• -2.5 V to +2.5 V	No
• -25 mV to +25 mV	No
• -250 mV to +250 mV	No
• -5 V to +5 V	Yes
— Input resistance (-5 V to +5 V)	10 MΩ
• -50 mV to +50 mV	No
• -500 mV to +500 mV	No
• -80 mV to +80 mV	No
<b>Cable length</b>	
• shielded, max.	200 m
<b>Analog value generation for the inputs</b>	
Measurement principle	integrating
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Integration time (ms)	2,5 / 16,67 / 20 / 100 ms
• Basic conversion time, including integration time (ms)	10 / 24 / 27 / 107 ms
— additional conversion time for wire-break monitoring	4 ms (to be considered for 1 to 5 V measurement)
• Interference voltage suppression for interference frequency $f_1$ in Hz	400 / 60 / 50 / 10 Hz
<b>Smoothing of measured values</b>	
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
<b>Encoder</b>	
<b>Connection of signal encoders</b>	
• for voltage measurement	Yes
<b>Errors/accuracies</b>	
Linearity error (relative to input range), (+/-)	0.1 %
Temperature error (relative to input range), (+/-)	0.006 %/K
Crosstalk between the inputs, max.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.1 %
<b>Operational error limit in overall temperature range</b>	
• Voltage, relative to input range, (+/-)	0.5 %
<b>Basic error limit (operational limit at 25 °C)</b>	
• Voltage, relative to input range, (+/-)	0.3 %
<b>Interference voltage suppression for <math>f = n \times (f_1 \pm 1 \%)</math>, <math>f_1</math> = interference frequency</b>	
• Series mode interference (peak value of interference < rated value of input range), min.	40 dB
• Common mode voltage, max.	4 V
• Common mode interference, min.	60 dB
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
<b>Diagnoses</b>	
• Monitoring the supply voltage	No
• Wire-break	Yes; Only for 1 ... 5 V
• Short-circuit	No
• Group error	No
• Overflow/underflow	Yes
<b>Diagnostics indication LED</b>	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• MAINT LED	No
• Monitoring of the supply voltage (PWR-LED)	No

<ul style="list-style-type: none"> <li>• Channel status display</li> </ul>	Yes; green LED
<ul style="list-style-type: none"> <li>• for channel diagnostics</li> </ul>	Yes; red LED
<ul style="list-style-type: none"> <li>• for module diagnostics</li> </ul>	Yes; red LED
<b>Potential separation</b>	
Potential separation channels	
<ul style="list-style-type: none"> <li>• between the channels</li> </ul>	No
<ul style="list-style-type: none"> <li>• between the channels, in groups of</li> </ul>	16
<ul style="list-style-type: none"> <li>• between the channels and backplane bus</li> </ul>	Yes
<b>Permissible potential difference</b>	
between the inputs (UCM)	8 V DC
Between the inputs and MANA (UCM)	4 V DC
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Ambient conditions</b>	
Ambient temperature during operation	
<ul style="list-style-type: none"> <li>• horizontal installation, min.</li> </ul>	-30 °C
<ul style="list-style-type: none"> <li>• horizontal installation, max.</li> </ul>	60 °C
<ul style="list-style-type: none"> <li>• vertical installation, min.</li> </ul>	-30 °C
<ul style="list-style-type: none"> <li>• vertical installation, max.</li> </ul>	40 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> <li>• Installation altitude above sea level, max.</li> </ul>	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
<b>Dimensions</b>	
Width	35 mm
Height	147 mm
Depth	129 mm
<b>Weights</b>	
Weight, approx.	250 g
<b>last modified:</b>	1/19/2021 