SIEMENS

Data sheet

6AG1620-0AA00-7AA0



SIPLUS PN/CAN link based on 6BK1620-0AA00-0AA0 with conformal coating, -40...+70 °C, from PROFINET to CAN/CANopen networks CAN 2.0 A/B CANopen manager to CiA301/302 CANopen slave to CiA301/302 IP20

General information		
Product type designation	PN/CAN Link	
Firmware version		
• FW update possible	Yes	
Vendor identification (VendorID)	ID 09 00 00 53h acc. to CiA	
Engineering with		
STEP 7 TIA Portal configurable/integrated from version	see entry ID: 109746275	
Installation type/mounting		
Mounting	DIN rail, wall mounting, portrait mounting	
Mounting position	any	
Recommended mounting position	Horizontal	
Rail mounting	Yes	
Control cabinet installation	Yes	
Supply voltage		
Type of supply voltage	DC	
Rated value (DC)	24 V	
permissible range, lower limit (DC)	20.4 V	
permissible range, upper limit (DC)	28.8 V	
Reverse polarity protection	Yes	
Overvoltage protection	Yes	
Short-circuit protection	Yes	
Mains buffering		
 Mains/voltage failure stored energy time 	10 ms	
Input current		
Current consumption (rated value)	0.09 A	
Current consumption, max.	0.11 A	
Power loss		
Power loss, typ.	2.2 W	
Interfaces		
Interfaces/bus type	2x Ethernet (RJ45), 1x Sub-D (9-pin)	
Supports protocol for PROFINET IO		
 automatic detection of transmission rate 	No	
Transmission rate, max.	100 Mbit/s	
Number of RJ45 ports	2	
 Number of FC (FastConnect) connections 	2	
PROFINET functions		
 Assignment of the IP address, supported 	Yes	
Assignment of the device name, supported	Yes	
1. Interface		
Interface type	CAN according to CiA 303-1	

Isolated	Yes: 500 V AC or 707 V DC
Interface types	
Number of ports	1
Design of the connection	9-pin sub D socket
CAN	
CAN operating modes	CAN Standard CAN 2.0A/B; CANopen Manager / Slave acc. to CiA
Specification acc. to CiA	CiA 301 & CiA 302
Transmission rate, min.	50 kbit/s
Transmission rate, max.	1 000 kbit/s
Number of slaves, max.	126
Number of SDOs in parallel	16; Parallel
Number of PDOs	512; Send / receive
Services	
— Node/life-guarding	Yes
— Heartbeat	Yes
- SYNC	Yes
2. Interface	
	DDOFINET
Interface type	PROFINET
Isolated	Yes; 1 500 V AC or 2 250 V DC
Interface types	Vac
RJ 45 (Ethernet)	Yes
Number of ports	2
integrated switch	Yes
Protocols	
PROFINET IO Device	Yes
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	Yes
Diagnostics function	Yes
Diagnostics indication LED	
RUN LED	Yes
• ERROR LED	Yes
MAINT LED	Yes
• LINK LED	Yes
• RX/TX LED	Yes
Potential separation	
Potential separation exists	Yes
Degree and class of protection	
IP degree of protection	IP20
Ambient conditions	
Ambient temperature during operation	
horizontal installation, min.	-40 °C; = Tmin (incl. condensation/frost)
horizontal installation, max.	70 °C; = Tmax
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	85 °C
Altitude during operation relating to sea level	
Installation altitude above sea level, max.	5 000 m
Ambient air temperature-barometric pressure-altitude	Tmin Tmax at 1 140 hPa 795 hPa (-1 000 m +2 000 m) // Tmin (Tmax
	- 10 K) at 795 hPa 658 hPa (+2 000 m +3 500 m) // Tmin (Tmax -20 K)
	at 658 hPa 540 hPa (+3 500 m +5 000 m)
Relative humidity	
 With condensation, tested in accordance with IEC 60068- 2-38, max. 	100 %; incl. condensation / frost permitted (no commissioning under condensation conditions)
Resistance	
I Coloid II CC	
Coolante and lubricente	
Coolants and lubricants	Vac hal diago and ail draplate in the sin
- Resistant to commercially available coolants and	Yes; Incl. diesel and oil droplets in the air
 Resistant to commercially available coolants and lubricants 	Yes; Incl. diesel and oil droplets in the air
 Resistant to commercially available coolants and lubricants Use in stationary industrial systems 	
 Resistant to commercially available coolants and lubricants 	Yes; Incl. diesel and oil droplets in the air Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request

60721-3-3	
 — to mechanically active substances according to EN 60721-3-3 	Yes; Class 3S4 incl. sand, dust, *
Use on ships/at sea	
 — to biologically active substances according to EN 60721-3-6 	Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on request
 — to chemically active substances according to EN 60721-3-6 	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
 — to mechanically active substances according to EN 60721-3-6 	Yes; Class 6S3 incl. sand, dust; *
Usage in industrial process technology	
 — Against chemically active substances acc. to EN 60654-4 	Yes; Class 3 (excluding trichlorethylene)
 Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04 	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
Remark	
 — Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04 	* The supplied plug covers must remain in place over the unused interfaces during operation!
Conformal coating	
 Coatings for printed circuit board assemblies acc. to EN 61086 	Yes; Class 2 for high reliability
 Protection against fouling acc. to EN 60664-3 	Yes; Type 1 protection
 Military testing according to MIL-I-46058C, Amendment 7 	Yes; Discoloration of coating possible during service life
 Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC- CC-830A 	Yes; Conformal coating, Class A
Dimensions	
Width	70 mm
Height	112 mm
Depth	75 mm
Weights	
Weight, approx.	212 g
last modified:	5/28/2022 🖸